

TCB INL THIRD 6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Inspired by 5S and lean management methods, Weidmüller foam inserts ensure an efficient and tidy workplace. Designed according to a modular principle, they offer many advantages and can be selected according to individual requirements.

General ordering data

Order No.	3155290000
Type	TCB INL THIRD 6
GTIN (EAN)	4099987654685
Qty.	1 items

TCB INL THIRD 6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	50 mm	Depth (inches)	1.9685 inch
Height	390 mm	Height (inches)	15.3543 inch
Width	185 mm	Width (inches)	7.2835 inch
Diameter	0 mm	Net weight	1042.01 g

Technical data

Description of article	Foam inlay universal big, empty
------------------------	---------------------------------

Tool chest

Assembly	with tools
----------	------------

Assortments

Diameter	0 mm
----------	------

Classifications

ETIM 8.0	EC011819	ETIM 9.0	EC011819
ETIM 10.0	EC011819	ECLASS 14.0	21-07-04-12
ECLASS 15.0	21-07-04-12		

TCB INL THIRD 6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Cable gland tools



Screwing tool for fixing and loosening cable glands and accessories in the sizes 11-36 AF.

- Can reach over several rows of glands
- No deforming of the cable glands
- Spanner size 11 to 36 mm
- Infinite adjustment of spanner size
- Ratchet function: not necessary to remove tool between turns
- Authentic one-hand tool

General ordering data

Type	FLECAFIX 11/24	Version
Order No.	9015900000	Cable gland tool
GTIN (EAN)	4032248309573	
Qty.	1 ST	
Type	FLECAFIX 24/36	Version
Order No.	9015980000	Cable gland tool
GTIN (EAN)	4032248309597	
Qty.	1 ST	

Screwty® cable gland tool



The ideal tool for any application

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

Type	SCREWTY SET	Version
Order No.	1910000000	Cable gland tool for M8, M12 lines and connectors
GTIN (EAN)	4032248436842	
Qty.	1 ST	