

U-NETOPS-LICENSE-1000-DEVICES-1Y**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Weidmüller u-netops is a tool to graphically represent a network of Ethernet Switches belonging to Advanced and Substation Lines. It also allows all the switches of the network to be configured and monitored.

The tool is based on SNMP for device detection and LLDP for link detection so any third-party device supporting these protocols can also be displayed on Weidmüller u-netops. The u-netops has a web-based user interface.

The network management tool operates as a web server, providing a browser-based user interface that is accessible from any PC within the network without the need for additional client software.

Key Benefits

- Centralized network management
- No client installation required
- Quick device discovery via SNMP
- Unified management for Weidmüller and third-party devices

General ordering data

Order No.	3236610000
Type	U-NETOPS-LICENSE-1000-DEVICES-1Y
Qty.	ST

U-NETOPS-LICENSE-1000-DEVICES-1Y

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	0 g
------------	-----

Temperatures

Storage temperature	Operating temperature
---------------------	-----------------------

Functions and features

Monitoring function	Topology visualization, Link status monitoring, Notifications (link down events), Real-time traffic monitoring, Historical traffic (up to 15 minutes), Traffic alarms	Device management function	Firmware upgrade (requires external TFTP server), Configuration backup / restore, Remote reboot, Host monitor (ICMP ping)
Security functions	Password policy, Management access security via privilege level configuration for different user roles		

System requirements

Operating system	Windows 11	Supported browser	Chrome, Firefox, Edge
------------------	------------	-------------------	-----------------------

Miscellaneous

Activation	The administrator enters the license key in u-netops (functions immediately available).	Included in delivery	Email with license key
------------	---	----------------------	------------------------

License

License duration	1 year	License renewal required	Yes
Licensing model	Per instance / per server	License deployment	On-premise (local installation, web-based)
Number of manageable devices	1000	License type	Subscription
Number of users	Unlimited		

Technical

Supported protocols	SNMP v1 / v2c / v3, LLDP, ICMP	Requirements for using third-party devices	via SNMP + LLDP (limited functionality)
Supported devices	Switches of AdvancedLine and SubstationLine, IE-SR-2TX (2-port router series)		

Classifications

ETIM 8.0	EC000809	ETIM 9.0	EC000809
ETIM 10.0	EC000809	ECLASS 14.0	27-24-25-01
ECLASS 15.0	27-24-25-01		

U-NETOPS-LICENSE-1000-DEVICES-1Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

