

SAIBWP-P-3A-3.5/5.5-M8**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female sockets for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M8 round plug-in connectors are particularly suited to applications where space is limited.

General ordering data

Version	Field attachable connector, M8
Order No.	3103380000
Type	SAIBWP-P-3A-3.5/5.5-M8
GTIN (EAN)	4099987149716
Qty.	1 items

SAIBWP-P-3A-3.5/5.5-M8

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Width	45 mm	Width (inches)	1.7716 inch
Diameter	14 mm	Net weight	16 g

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data customisable plug-in connectors

Number of poles	3	
Coding	none	
Contact surface	Ni/Au	
Type of connection	PUSH IN	
Housing main material	PBT diecast zinc	
Cable diameter, max.	5.5 mm	
Cable diameter, min.	3.5 mm	
Contact material	CuSn	
Conductor cross-section, max.	0.5 mm ²	
Conductor cross-section, min.	0.14 mm ²	
Nominal current	4 A	
Protection degree	IP67	
Plugging cycles	≥ 100	
Pollution severity	3	
Gender of contact	Female	
Rated voltage	Rated voltage	48 V
	Voltage type	AC
	Rated voltage	60 V
	Voltage type	DC
Shield connection	No	
Threaded ring material	Diecast zinc	
Temperature range of housing	-25...+85 °C	
Connection cross-section, max.	0.5 mm ²	
Connection cross-section, min.	0.14 mm ²	

Standards

Connector standard	IEC 61076-2-104
--------------------	-----------------

Classifications

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		


SAIBWP-P-3A-3.5/5.5-M8

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings

Dimensioned drawing



Pole scheme



Similar to illustration



