

TS 35X7.5/LL 2M/ST/SZ**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Version	Terminal rail, Accessories, Steel, galvanic zinc plated and passivated, Width: 2000 mm, Height: 35 mm, Depth: 7.5 mm
Order No.	7915060000
Type	TS 35X7.5/LL 2M/ST/SZ
GTIN (EAN)	4032248296279
Qty.	40 M

TS 35X7.5/LL 2M/ST/SZ

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	7.5 mm	Depth (inches)	0.2953 inch
Height	35 mm	Height (inches)	1.378 inch
Width	2000 mm	Width (inches)	78.74 inch
Net weight	300 g		

Temperatures

Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Mounting rail

Solder eyelet hole diameter (D)	5.2 mm		
Installation advice	Direct mounting		
Standards	DIN EN 60715		
Surface finish	galvanic zinc plated and passivated		
Thickness	1.00 mm		
Basic material	Steel		
Length of the terminal rail	min.	0 mm	
	nominal	2000 mm	
	max.	2000 mm	
Slotted drill holes	Yes		
Slit length	25.00 mm		
Slit gap	11.00 mm		
Short-time withstand current per second according to IEC 60947-7-2	1.92 kA		
Slit width	5.20 mm		
Pre-punched mounting rail	Yes		
Slit width			
Short circuit strength corresponds to E-Cu wire	16.00 mm ²		
Drill-hole diameter	5.20 mm		
Spacing of holes, centre-to-centre	36 mm		
Slit gap			
Slit length			

Important note

Product information Din rails with Sendzimier treatment have limited corrosion resistance on the outer and cut edges

Classifications

ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		

TS 35X7.5/LL 2M/ST/SZ

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

