

**TS15X5 ST K4**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Similar to illustration****Similar to illustration**

The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS15
- Mounting plates
- Hinges
- Wall-mounted holder

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.

**General ordering data**

|            |   |
|------------|---|
| Version    | Rail, TS 15, Width: 64 mm, without slot, Steel, galvanized, chromium-plated |
| Order No.  | <a href="#">8000037609</a>  |
| Type       | TS15X5 ST K4  |
| GTIN (EAN) | 4050118682489   |
| Qty.       | 20 items  |

## TS15X5 ST K4

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

|      |         |
|------|---------|
| RoHS | Conform |
|------|---------|

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 5.5 mm | Depth (inches)  | 0.2165 inch |
| Height     | 15 mm  | Height (inches) | 0.5906 inch |
| Width      | 64 mm  | Width (inches)  | 2.5197 inch |
| Net weight | 6 g    |                 |             |

## Temperatures

Operating temperature

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## General information

|                    |                             |                |              |
|--------------------|-----------------------------|----------------|--------------|
| Material thickness | 1 mm                        | Standards      | DIN EN 60715 |
| Surface finish     | galvanized, chromium-plated | Basic material | Steel        |

## General information on accessories

|                    |       |                |                             |
|--------------------|-------|----------------|-----------------------------|
| Material thickness | 1 mm  | Surface finish | galvanized, chromium-plated |
| Basic material     | Steel |                |                             |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001285    | ETIM 9.0    | EC001285    |
| ETIM 10.0   | EC001285    | ECLASS 14.0 | 27-40-06-02 |
| ECLASS 15.0 | 27-40-06-02 |             |             |

**TS15X5 ST K4**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****Mounting support**

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

|            |                            |   |
|------------|----------------------------|---|
| Type       | FKSC M5X8 D9/SW2.5         | Version   |
| Order No.  | <a href="#">0295900000</a> | SAK Series, Allen hex screw, Screws, Number of poles: 1 |
| GTIN (EAN) | 4008190133337              |   |
| Qty.       | 50 ST                      |   |