

TS35X7.5 ST KEBI 30 VER

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



Similar to illustration

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the Klippon® EBi enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Terminal rails

The TS35 terminal rail is available in various lengths for mounting DIN rails (e.g. electronics, terminals) components in the enclosures.

General ordering data

Version	Rail, TS 35, TS 35 x 7.5, Width: 229 mm, without slot, Steel, galvanized, chromium-plated
Order No.	8000037556
Type	TS35X7.5 ST KEBI 30 VER
GTIN (EAN)	4050118653090
Qty.	20 items

TS35X7.5 ST KEBI 30 VER

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	7.5 mm	Depth (inches)	0.2953 inch
Height	35 mm	Height (inches)	1.378 inch
Width	229 mm	Width (inches)	9.0157 inch
Net weight	77.72 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General information

Material thickness	1 mm	Standards	DIN EN 60715
Surface finish	galvanized, chromium-plated	Basic material	Steel
Integral fixing	Screwed		

Classifications

ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		

TS35X7.5 ST KEBI 30 VER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Mounting plates



Mounting plates, with and without hole patterns, for longitudinal and transverse mounting of DIN mounting rails or components directly onto the mounting plate.

General ordering data

Type	GFSC M5X10 TX20 SET	Version	
Order No.	1274150000	Klippon EB (Essential Box), Mounting screw, Height: 13.3 mm, Width:	
GTIN (EAN)	4050118063820	8.5 mm, Depth: 8.5 mm, Basic material: Steel, galvanized, galvanic	
Qty.	1 ST	zinc plated and passivated, silver	