

**TS35X15 ST KTB2215 VER****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Similar to illustration

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

**Terminal rails**

The mounting rails are available in two sizes for mounting DIN rails (e.g. electronics, terminals) components in the enclosures.

**General ordering data**

|            |                                                                                                  |
|------------|--------------------------------------------------------------------------------------------------|
| Version    | Rail, TS 35, TS 35 x 15, Width: 174 mm, without slot, Steel, galvanic zinc plated and passivated |
| Order No.  | <a href="#">8000073109</a>                                                                       |
| Type       | TS35X15 ST KTB2215 VER                                                                           |
| GTIN (EAN) | 4064675340591                                                                                    |
| Qty.       | 20 items                                                                                         |

## TS35X15 ST KTB2215 VER

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 15 mm    | Depth (inches)  | 0.5906 inch |
| Height     | 35 mm    | Height (inches) | 1.378 inch  |
| Width      | 174 mm   | Width (inches)  | 6.8504 inch |
| Net weight | 119.88 g |                 |             |

## Temperatures

Operating temperature

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## General information

|                    |              |                     |                                     |
|--------------------|--------------|---------------------|-------------------------------------|
| Material thickness | 1.5 mm       | Installation advice | Direct mounting                     |
| Standards          | DIN EN 60715 | Surface finish      | galvanic zinc plated and passivated |
| Basic material     | Steel        | Integral fixing     | Screwed                             |

## General information on accessories

|                    |        |                |                                     |
|--------------------|--------|----------------|-------------------------------------|
| Material thickness | 1.5 mm | Surface finish | galvanic zinc plated and passivated |
| Basic material     | Steel  |                |                                     |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001285    | ETIM 9.0    | EC001285    |
| ETIM 10.0   | EC001285    | ECLASS 14.0 | 27-40-06-02 |
| ECLASS 15.0 | 27-40-06-02 |             |             |