



PV CPCI22TXUXDXAXWXRXWW
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com


Connecting photovoltaic power plants through reliable and safe industrial communications.

Weidmüller combined its extensive experience with photovoltaic projects and industrial communication to create this portfolio of PV Communication Boxes. For this portfolio we developed 2 different product ranges:

- The "Premium" family is our most robust product. Designed to offer constant connectivity thanks to its backup power system. And thereby offers you reliability and power in one solution.
- The new "Lite" family offers you the same signal connectivity on site as the "Premium" version, but in a more compact version.

General ordering data

Version	Photovoltaics, Assembled enclosure, Communication module, 230 V AC, Surge protection I, Battery powered, Current monitoring, Monitoring components, Voltage monitoring, Limit value monitoring, Communication Box, RJ45
Order No.	8000111621
Type	PV CPCI22TXUXDXAXWXRXWW
GTIN (EAN)	4099986678880
Qty.	1 items
Delivery status	Discontinued

PV CPC122TXUXDXAXWXRWW

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	180 mm	Depth (inches)	7.0866 inch
Height	270 mm	Height (inches)	10.6299 inch
Width	360 mm	Width (inches)	14.1732 inch
Net weight	4000 g		

Temperatures

Ambient temperature -10 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	d33ac1e5-d9b3-45a8-b552-8b15f2a45207

DC electrical properties

Rated voltage	230 V	Surge protection AC side	PU I 1+1 LCF 280V/12,5kA, without auxiliary contact
Earthing	Directly at the VPU	Surge protection WIA RS485 side (string monitoring)	No

DC inputs

Number of inputs	1	Number of conduit inlets	3
------------------	---	--------------------------	---

DC string monitoring

Supply	Battery PRO ECO 72W 24V 3A	Monitoring function	Industrial PC, Industrial Ethernet router with RJ45 ports, Connection between field devices to SCADA through RS-485
Voltage monitoring	Yes		

Classifications

ETIM 8.0	EC003857	ETIM 9.0	EC003857
ETIM 10.0	EC003857	ECLASS 14.0	22-57-02-92
ECLASS 15.0	22-57-02-92		

PV CPCI22TXUXDXAXWXRXWW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

