

## RS 4XRJ12

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Multiple data distributor in the meter cabinet for the TS35

### General ordering data

Order No.	8000112157
Type	<a href="#">RS 4XRJ12</a>
GTIN (EAN)	4099987025591
Qty.	10 items

## RS 4XRJ12

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Depth	21.5 mm	Depth (inches)	0.8465 inch
Height	80.2 mm	Height (inches)	3.1575 inch
Width	17.9 mm	Width (inches)	0.7047 inch
Net weight	19 g		

### Temperatures

Storage temperature	-25...70 °C	Operating temperature	-20...55 °C
Humidity at operating temperature	0...85% (no condensation)		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Connection data

Distribution PCB connectors	4 x RJ12 plug-in connectors
-----------------------------	-----------------------------

### Rating data

Protection degree	IP20	Rated voltage	< 150 V AC
Operating voltage	150 V AC	Maximum current per distributor connection	1 A

### Insulation coordination (EN 60664-1)

Rated insulation voltage	<150 V AC	Surge voltage category	II
Pollution severity	2	Pulse voltage test (1,2/50 µs)	1.5 kV

### Connection field

Type of connection	Plug-in connection
--------------------	--------------------

### Supply connection

Type of connection	Plug-in connection
--------------------	--------------------

### Important note

IPC conformity	Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.
----------------	--

## Technical data

### Classifications

ETIM 8.0	EC002780	ETIM 9.0	EC002780
ETIM 10.0	EC002780	ECLASS 14.0	27-14-11-52
ECLASS 15.0	27-14-11-52		

RS 4XRJ12

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

Drawings

www.weidmueller.com

