

KTB GP 76XX15V CD S4 PE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

General ordering data

| | |
|------------|---|
| Order No. | 8000114902 |
| Type | KTB GP 76XX15V CD S4 PE |
| GTIN (EAN) | 4099986797437 |
| Qty. | 1 items |

KTB GP 76XX15V CD S4 PE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

| | | | |
|------------|---------|-----------------|--------------|
| Depth | 3 mm | Depth (inches) | 0.1181 inch |
| Height | 345 mm | Height (inches) | 13.5826 inch |
| Width | 117 mm | Width (inches) | 4.6063 inch |
| Net weight | 967.4 g | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General information

| | | | |
|--------------------|------------------|-----------------------|-------------------------------|
| Material thickness | 3 mm | Installation advice | Screw mounting |
| Surface finish | electropolished | Basic material | Stainless steel 1.4404 (316L) |
| Integral fixing | Screwed | Protection class (UL) | Type 3, Type 4X, Type 12 |
| Gland plates | left, right | Flange plate | Yes |
| Areas of use | Process industry | | |

General information on accessories

| | | | |
|--------------------|-----------------|---------------------------------|-------------------------------|
| Material thickness | 3 mm | Solder eyelet hole diameter (D) | 7 mm |
| Surface finish | electropolished | Basic material | Stainless steel 1.4404 (316L) |

Housing earth

| | |
|-----------------------|--|
| Flange plate earthing | Welded-on M6 x 10 stainless-steel earth stud |
|-----------------------|--|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000211 | ETIM 9.0 | EC000211 |
| ETIM 10.0 | EC000211 | ECLASS 14.0 | 27-14-24-21 |
| ECLASS 15.0 | 27-14-24-21 | | |