


PV SUNCOVER 30/56/21**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Photovoltaics, Sun cover
Order No.	8000196680
Type	PV SUNCOVER 30/56/21
GTIN (EAN)	4069165146783
Qty.	1 items

PV SUNCOVER 30/56/21

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Approvals**

Approvals



ROHS

Conform

Dimensions and weights

Depth	213.3 mm	Depth (inches)	8.3976 inch
Height	326.5 mm	Height (inches)	12.8543 inch
Width	599 mm	Width (inches)	23.5826 inch
Net weight	6000 g		


Material

Basic material

Stainless steel

Classifications

ETIM 8.0	EC000744	ETIM 9.0	EC000744
ETIM 10.0	EC000744	ECLASS 14.0	27-18-24-05
ECLASS 15.0	27-18-24-05		



PV SUNCOVER 30/56/21

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

DC generator combiner boxes without fuses



PV Next combiner boxes for inverters with 1 to 12 MPP trackers are used to protect the DC side of a photovoltaic system. The combiner boxes protect the inverter against overvoltages and thus comply with the European Directive CLC/TS 51643-32. In addition, these products offer the possibility to protect the system against reverse currents and the possibility to combine strings to save cables during installation.

General ordering data

Type	PVN1M3I9SXFV100TXPX10	Version
Order No.	2683130000	Photovoltaics, Combiner Box, PV Next, 1000 V, 3 MPP's, 3 Inputs / 3
GTIN (EAN)	4050118699876	Outputs per MPP, Surge protection I / II, Cable gland
Qty.	1 ST	
Type	PVN1M3I9SXFV101TXPX10	Version
Order No.	2683190000	Photovoltaics, Combiner Box, PV Next, 1000 V, 3 MPP's, 3 Inputs / 3
GTIN (EAN)	4050118700220	Outputs per MPP, Surge protection I / II, WM4C
Qty.	1 ST	
Type	PVN1M3I9SXFV200TXPX10	Version
Order No.	2683330000	Photovoltaics, Combiner Box, PV Next, 1000 V, 3 MPP's, 3 Inputs / 3
GTIN (EAN)	4050118700152	Outputs per MPP, Surge protection II, Cable gland
Qty.	1 ST	
Type	PVN1M6I4SXFV100TXPX10	Version
Order No.	2737630000	Photovoltaics, Combiner Box, PV Next, 1000 V, 6 MPP's, 2 Inputs / 1
GTIN (EAN)	4050118824902	Output per MPP, Surge protection I / II, Cable gland
Qty.	1 ST	
Type	PVN1M6I4SXFV101TXPX10	Version
Order No.	2737620000	Photovoltaics, Combiner Box, PV Next, 1000 V, 6 MPP's, 2 Inputs / 1
GTIN (EAN)	4050118824896	Output per MPP, Surge protection I / II, WM4C
Qty.	1 ST	

DC generator combiner boxes with fuses



PV Next combiner boxes for inverters with 1 to 12 MPP trackers are used to protect the DC side of a photovoltaic system. The combiner boxes protect the inverter against overvoltages and thus comply with the European Directive CLC/TS 51643-32. In addition, these products offer the possibility to protect the system against reverse currents and the possibility to combine strings to save cables during installation.

General ordering data

Type	PVN DC 3IF 30 2MPP SPD1...	Version
Order No.	2683040000	Photovoltaics, Combiner Box, PV Next, 1000 V, 2 MPP's, 3 Inputs /
GTIN (EAN)	4050118699715	3 Outputs per MPP, With fuse holder, Surge protection I / II, Cable
Qty.	1 ST	gland

PV SUNCOVER 30/56/21

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	PVN DC 3IF 30 2MPP SPD1...	Version
Order No.	2683080000	Photovoltaics, Combiner Box, PV Next, 1000 V, 2 MPP's, 3 Inputs / 3
GTIN (EAN)	4050118699913	Outputs per MPP, With fuse holder, Surge protection I / II, WM4C
Qty.	1 ST	
Type	PVN DC 6IF 70 1MPP SPD1...	Version
Order No.	2737520000	Photovoltaics, Combiner Box, PV Next, 1000 V, 1 MPP, 6 Inputs /
GTIN (EAN)	4050118004595	6 Outputs per MPP, With fuse holder, Surge protection I / II, Cable
Qty.	1 ST	gland
Type	PVN DC 6IF 70 1MPP SPD1...	Version
Order No.	2737440000	Photovoltaics, Combiner Box, PV Next, 1000 V, 1 MPP, 6 Inputs / 6
GTIN (EAN)	4032248395545	Outputs per MPP, With fuse holder, Surge protection I / II, WM4C
Qty.	1 ST	