

KEBIQL304020S2N0 AL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

**General ordering data**

Version	Klippon EBi QL (Essential Box industrial - Quarter Lock), Enclosures, straight, Height: 300 mm, Width: 400 mm, Depth: 200 mm, Basic material: Stainless steel 1.4301 (304), Brushed, untreated, silver
Order No.	8000133639
Type	KEBIQL304020S2N0 AL
GTIN (EAN)	4099987368575
Qty.	1 items

KEBIQL304020S2N0 AL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



Dimensions and weights

Depth	200 mm	Depth (inches)	7.874 inch
Height	300 mm	Height (inches)	11.811 inch
Width	400 mm	Width (inches)	15.748 inch
Net weight	6825.84 g		

Temperatures

Operating temperature -40 °C...85 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Cable glands, right

M25	10	M16	32
M40	5	M32	8
M20	21	M12	55

Cable glands, top/bottom

M20	70	M12	85
M40	15	M32	24
M25	40	M16	96

Certificate numbers enclosure

Declaration of Conformity No. (DoC LVD) DE PS2650 220428 001ISS01 Approval conditions CE

General information

Material thickness of cover	1.5 mm	Material thickness of enclosure	1.5 mm
Material thickness	1.5 mm	Operating temperature, max.	85 °C
Operating temperature, min.	-40 °C	Surface finish	Brushed, untreated
Impact resistance	10 J version standard	Protection degree	IP66
Basic material	Stainless steel 1.4301 (304)	Seal material	Polyurethane
Enclosure attachment	4 or 6, M6 blind thread hole on backside; optionally via additional mounting feet	Flange plate	No
Lid	Yes	Areas of use	Building systems and technology

KEBIQL304020S2N0 AL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Housing earth

Earth, enclosure, cover	Welded-on M6 stainless-steel earth stud in enclosure body and lid.	Earth, enclosure, external	Welded-on M6 stainless-steel earth stud in enclosure body and lid.
Earth, enclosure, internal	Welded-on M6 stainless-steel earth stud in enclosure body and lid.		

horizontal assembly

WDU 10 / ZDU 10	3x21	WDU 16 / ZDU 16	3x18
WDU 2,5 / ZDU 2,5 / IDU 2,5	3x42	WDU 35 / ZDU 35	3x13
WDU 4 / ZDU 4	3x35	WDU 6 / ZDU 6	3x27

vertical assembly

WDU 10 / ZDU 10	3x51	WDU 16 / ZDU 16	3x40
WDU 2,5 / ZDU 2,5 / IDU 2,5	3x61	WDU 35 / ZDU 35	3x19
WDU 4 / ZDU 4	3x51	WDU 6 / ZDU 6	3x40

Classifications

ETIM 8.0	EC000261	ETIM 9.0	EC000261
ETIM 10.0	EC000261	ECLASS 14.0	27-18-01-01
ECLASS 15.0	27-18-01-01		