

TS35X15 ST 202 K75 VER**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Similar to illustration

The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS15
- Mounting plates
- Hinges
- Wall-mounted holder

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

Version	Rail, TS 35 x 15, Width: 202 mm, without slot, with slot, Steel, galvanic zinc plated and passivated
Order No.	8000135666
Type	TS35X15 ST 202 K75 VER
GTIN (EAN)	4099987090049
Qty.	1 items

TS35X15 ST 202 K75 VER

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	15 mm	Depth (inches)	0.5906 inch
Height	35 mm	Height (inches)	1.378 inch
Width	202 mm	Width (inches)	7.9527 inch
Length	202 mm	Length (inches)	7.9527 inch
Net weight	144.84 g		

Temperatures

Ambient temperature	-5 °C...40 °C	Operating temperature	
---------------------	---------------	-----------------------	--

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Material thickness	1.5 mm	Installation advice	Direct mounting
Standards	In accordance with DIN EN 60715	Surface finish	galvanic zinc plated and passivated
Basic material	Steel	Stamp dimensions	6.3 x 20 mm

General information on accessories

Material thickness	1.5 mm	Surface finish	galvanic zinc plated and passivated
Basic material	Steel	Stamp dimensions	6.3 x 20 mm

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 9.0	27-40-06-02
ECLASS 9.1	27-40-06-02	ECLASS 10.0	27-40-06-02
ECLASS 11.0	27-40-06-02	ECLASS 12.0	27-40-06-02
ECLASS 13.0	27-40-06-02	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		