

PV SUNCOVER 20/30/13

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Photovoltaics, Sun cover
Order No.	8000143249
Type	PV SUNCOVER 20/30/13
GTIN (EAN)	4099987111881
Qty.	1 items

PV SUNCOVER 20/30/13

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	136.5 mm	Depth (inches)	5.374 inch
Height	241 mm	Height (inches)	9.4882 inch
Width	324.5 mm	Width (inches)	12.7756 inch
Net weight	2050 g		

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%


Material

Basic material Stainless steel

Classifications

ETIM 8.0	EC000744	ETIM 9.0	EC000744
ETIM 10.0	EC000744	ECLASS 14.0	27-18-24-05
ECLASS 15.0	27-18-24-05		

Drawings



PV SUNCOVER 20/30/13

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Fireman Switch



For safe remote shutdown Rooftop photovoltaic systems can require a disconnection device at the point where the cables enter into the building, that is connected to the power grid in the building. This allows the fire brigade to carry out their work in an emergency without being unnecessarily endangered. When the power supply is restored, the PV Next Fireman Switch automatically reconnects the PV strings.

General ordering data

Type	PVC DC 2I 1O 2MPP RD SP...	Version
Order No.	8000098970	Photovoltaics, Combiner Box, Fireman's switch, PV Next, 1100 V, 2
GTIN (EAN)	40999866665293	MPP's, 2 Inputs / 1 Output per MPP, Surge protection I / II, Remote
Qty.	1 ST	disconnecter, MC4-Evo 2
Type	PVC DC 2I 1O 2MPP RD SP...	Version
Order No.	8000114374	Photovoltaics, Combiner Box, Fireman's switch, PV Next, 1100 V, 2
GTIN (EAN)	4099986766976	MPP's, 2 Inputs / 1 Output per MPP, Surge protection I / II, Remote
Qty.	1 ST	disconnecter, WM4C