

**MBGE ADPT IPC 621,24 POLE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

---

Adapters for migration – IPC 621.

The front adapters with pre-assembled cables provide a safe migration from the IPC 621 cards to other PLC/DCS systems or the u-remote modules from Weidmüller.

**General ordering data**

Order No.	8000148516
Type	<a href="#">MBGE ADPT IPC 621,24 POLE</a>
GTIN (EAN)	4099987193405
Qty.	ST

## MBGE ADPT IPC 621,24 POLE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	72.2 mm	Depth (inches)	2.8425 inch
Height	152.4 mm	Height (inches)	6 inch
Width	29.2 mm	Width (inches)	1.1496 inch
Net weight	0.05 g		

### Temperatures

Storage temperature	-20...70 °C	Operating temperature	-20...50 °C
---------------------	-------------	-----------------------	-------------

### Rated data UL

Storage temperature UL, max.	70 °C	Operating temperature UL, min.	-20 °C
Operating temperature UL, max.	50 °C	Storage temperature UL, min.	-20 °C
Rated current I <sub>max</sub>	20 A	Rated voltage UN	250 V

### Connection data

Number of poles (control side)	24-pole	Connection (field side)	IPC 621 24 pole connector
--------------------------------	---------	-------------------------	---------------------------

### Connection data

Connection (field side)	IPC 621 24 pole connector	Connection to PLC	New PLC terminal block or hardwired
Number of poles (field side)	24 P		

### Ratings data

Operating voltage	250 V	Max. current per channel	6 A
Total operating current	20 A		

### Insulation coordination (EN50178)

Rated insulation voltage	300 V	Surge voltage category	II
Pollution severity level	2	Pulse voltage test (1,2/50µs)	2.5 kV
Insulation test voltage AC	1.8 kV		

### Classifications

ETIM 8.0	EC002584	ETIM 9.0	EC002584
ETIM 10.0	EC002584	ECLASS 14.0	27-33-02-92
ECLASS 15.0	27-33-02-92		

**MBGE ADPT IPC 621,24 POLE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

