

MBGE ADPT, 505-4232A 40 POLE DI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Adapters for migration – Siemens 505.

The front adapters with pre-assembled cables provide a safe migration from Siemens 505 cards to other PLC/DCS systems or the u-remote modules from Weidmüller.

General ordering data

Order No.	8000149534
Type	MBGE ADPT, 505-4232A 40 POLE DI
GTIN (EAN)	4099987229357
Qty.	ST

MBGE ADPT, 505-4232A 40 POLE DI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	64.17 mm	Depth (inches)	2.5264 inch
Height	179.66 mm	Height (inches)	7.0732 inch
Width	20 mm	Width (inches)	0.7874 inch
Net weight	0.05 g		

Temperatures

Storage temperature	-20...70 °C	Operating temperature	-20...50 °C
---------------------	-------------	-----------------------	-------------

Rated data UL

Storage temperature UL, max.	70 °C	Operating temperature UL, min.	-20 °C
Operating temperature UL, max.	50 °C	Storage temperature UL, min.	-20 °C
Rated current I _{max}	40 A	Rated voltage UN	250 V

Connection data

Number of poles (control side)	40-pole	Connection (field side)	Siemens 505-4232A or 4332 PLC 40 pole connector
--------------------------------	---------	-------------------------	---

Connection data

Connection (field side)	Siemens 505-4232A or 4332 PLC 40 pole connector	Connection to PLC	New PLC terminal block or hardwired
Number of poles (field side)	40 P		

Ratings data

Operating voltage	250 V	Max. current per channel	3.96 A
Total operating current	40 A		

Insulation coordination (EN50178)

Rated insulation voltage	300 V	Surge voltage category	II
Pollution severity level	2	Pulse voltage test (1,2/50µs)	2.5 kV
Insulation test voltage AC	1.8 kV		

Classifications

ETIM 8.0	EC002584	ETIM 9.0	EC002584
ETIM 10.0	EC002584	ECLASS 14.0	27-33-02-92
ECLASS 15.0	27-33-02-92		

MBGE ADPT, 505-4232A 40 POLE DI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

