

IE-S-IP67

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Junction box, design for SnapIn plug-in connectors ver.6
according to IEC 61076-3-106, plastic

General ordering data

Version	Connecting plug, Junction box, IP67, Cat.6A / Class EA (ISO/IEC 11801 2010), Variant 6 to IEC 61076-3-106
Order No.	8808370000
Type	IE-S-IP67
GTIN (EAN)	403224850595 1
Qty.	1 items

IE-S-IP67

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 90 g

Temperatures

Storage temperature Installation temperature Operating temperature -40 °C...70 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Colour	Light Grey	Housing main material	PA 66, UL 94: V-0
Type of mounting	Floor-mounted, for exposed connections, Wall mounting	Protection degree	IP67
Plugging cycles	750	Composition	Screw-on junction box including RJ45 module with IDC connection
Wiring	EIA/TIA T568 A, EIA/TIA T568 B		

General standards

Certificate No. (DNV) TAE00003EW Connector standard IEC 61076-3-106 Var. 6

Technical data RJ45 module

Wiring EIA/TIA T568 A, EIA/TIA T568 B

Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

Drawings

Dimensioned drawing



IE-S-IP67

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

... for modular plug-in connectors



Crimping tools for modular plug-in connector systems WE and DEC

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- Three functions in one tool

General ordering data

Type	TT 8 RS MP 8	Version	
Order No.	9202800000	Pressing tools, Crimping tool for contacts	
GTIN (EAN)	4032248512072		
Qty.	1 ST		

Sets - RJ45

SnapIn plug-in connectors according to IEC 61076-3-106 ver.6 in plastic, with RJ45 insert



General ordering data

Type	IE-P-IP67	Version	
Order No.	8808380000	Connecting plug, Plug, IP67, Cat.6A / Class EA (ISO/IEC 11801	
GTIN (EAN)	4032248505968	2010), Variant 6 to IEC 61076-3-106	
Qty.	1 ST		