

## IE-P-IP67

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



SnapIn plug-in connectors according to IEC 61076-3-106 ver.6 in plastic, with RJ45 insert

### General ordering data

Version	Connecting plug, Plug, IP67, Cat.6A / Class EA (ISO/IEC 11801 2010), Variant 6 to IEC 61076-3-106
Order No.	<a href="#">8808380000</a>
Type	IE-P-IP67
GTIN (EAN)	4032248505968
Qty.	1 items

**IE-P-IP67**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Net weight 29 g

**Temperatures**

Storage temperature Installation temperature Operating temperature -40 °C...70 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

Connection 1	RJ45	Connection 2	IDC
Description of article	Plug	Wiring	EIA/TIA T568 A
Colour	Light Grey	Housing main material	PA 66, UL 94: V-0
Category	Cat.6A / Class EA (ISO/ IEC 11801 2010)	Contact surface	Gold over nickel
Type of mounting	Floor-mounted, for exposed connections, Wall mounting	Shielding	360°; shield contact
Protection degree	IP67	Plugging cycles	750


**General standards**

Certificate No. (DNV) TAE00003EW Connector standard IEC 61076-3-106 Var. 6, IEC 60603-7-5

**Classifications**

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

**Dimensioned drawing**



## IE-P-IP67

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## ... for modular plug-in connectors



Crimping tools for modular plug-in connector systems WE and DEC

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- Three functions in one tool

## General ordering data

Type	TT 8 RS MP 8	Version	
Order No.	<a href="#">9202800000</a>	Pressing tools, Crimping tool for contacts	
GTIN (EAN)	4032248512072		
Qty.	1 ST		

## RJ45 crimp



RJ45 crimp plug-in connector according to IEC 60603-7-51 for wire outer diameters up to 1.05 mm

## General ordering data

Type	IE-PM-RJ45-TH	Version	
Order No.	<a href="#">1963580000</a>	RJ45 crimp plug, Plug without bending protection sleeve, Cat.6A /	
GTIN (EAN)	4032248645688	Class EA (ISO/IEC 11801 2010)	
Qty.	100 ST		

## IE-P-IP67

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Counterpart

www.weidmueller.com

## Sets - RJ45

SnapIn plug-in connectors according to IEC 61076-3-106 ver.6 in plastic, with RJ45 insert



## General ordering data

Type	IE-XM-6D-RJ45/RJ45-IP67	Version
Order No.	<a href="#">8829450000</a>	Mounting flange, Coupling flange, 90° down, Cat.6 (ISO/IEC 11801),
GTIN (EAN)	4032248532476	IP67
Qty.	1 ST	
Type	IE-XM-6U-RJ45/RJ45-IP67	Version
Order No.	<a href="#">8829440000</a>	Mounting flange, Coupling flange, 90° up, Cat.6 (ISO/IEC 11801),
GTIN (EAN)	4032248532469	IP67
Qty.	1 ST	
Type	IE-XM-RJ45/IDC-IP67	Version
Order No.	<a href="#">8808440000</a>	Mounting flange, RJ45 module flange, straight, Cat.6A / Class EA
GTIN (EAN)	4032248506026	(ISO/IEC 11801 2010), IP67
Qty.	1 ST	
Type	IE-XM-RJ45/RJ45-IP67	Version
Order No.	<a href="#">8808450000</a>	Mounting flange, Coupling flange, straight, Cat.6A / Class EA (ISO/
GTIN (EAN)	4032248506033	IEC 11801 2010), IP67
Qty.	1 ST	