

HTX 138

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Crimping tools for coaxial connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Pressing tool, Crimping tool for contacts, Hexagonal crimp
Order No.	901240000
Type	HTX 138
GTIN (EAN)	4008 190036546
Qty.	1 items

HTX 138

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Net weight	415.08 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Description of article	Crimping tool for Twinax coaxial cable / AF 8.24	Version	Mechanical, without interchangeable inserts
------------------------	--	---------	---

Description of contact

Type of contact	Coaxial connector
-----------------	-------------------

tool data crimping

Hexagon spanner width (A 2)	1.72 mm	Hexagon AF (A)	8.24 mm
Wire end ferrules cross-section, max.	70 mm ²	Wire end ferrules cross-section, min.	4 mm ²
Diameter of outer sleeve	9.5 mm	Crimping station, width (B 2)	2.3 mm
Crimping station, width (B 1)	10 mm	Crimping type/profile	Hexagonal crimp
Internal contact diameter (D)	2 mm		

Classifications


ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		

HTX 138

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



HTX 138

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Accessories / replacement parts



Crimping tools for coaxial connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Type	ERTE ES HTX 138	Version	
Order No.	9003140000	Pressing tool, Replacement part	
GTIN (EAN)	4008190025229		
Qty.	1 ST		