

HTI 15 ZERT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Crimping tools for insulated connectors
cable lugs, terminal pins, parallel and serial connectors,
plug-in connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.
- Tested to DIN EN 60352 part 2

General ordering data

Version	Pressing tool, Tool for insulated cable connectors, 0.5mm ² , 2.5mm ² , Double crimp
Order No.	9017430000
Type	HTI 15 ZERT
GTIN (EAN)	4008190865344
Qty.	1 items

HTI 15 ZERT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Net weight	453.2 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Description of article	Crimping tool for insulated connectors, 0.5-2.5 mm ²	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

Description of contact

Type of contact	Insulated connector	Conductor cross-section, max. AWG	AWG 14
Conductor cross-section, min. AWG	AWG 21	Crimping range, max.	2.5 mm ²
Crimping range, min.	0.5 mm ²		

tool data crimping

Wire end ferrules cross-section, max.	2.5 mm ²	
Crimping type/profile	Double crimp	
Crimping station	Crimping station number	1
	Conductor cross-section, min.	0.5 mm ²
	Conductor cross-section, max.	1.5 mm ²
	Conductor cross-section AWG, min.	21 AWG
	Conductor cross-section AWG, max.	16 AWG
	Colour of crimping station	Red
	Crimping station number	2
	Conductor cross-section, min.	1.5 mm ²
	Conductor cross-section, max.	2.5 mm ²
	Conductor cross-section AWG, min.	16 AWG
	Conductor cross-section AWG, max.	14 AWG
	Colour of crimping station	Blue

Important note

Product information	Not suitable for solid conductors. Insulation on the contact is pressed conically.
---------------------	--

Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		




HTI 15 ZERT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Accessories

www.weidmueller.com

Accessories / replacement parts



Crimping tools for insulated connectors
cable lugs, terminal pins, parallel and serial connectors,
plug-in connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.
- Tested to DIN EN 60352 part 2

General ordering data

Type	ERTE ES HTI 15	Version
Order No.	1246370000	Pressing tool, Replacement part
GTIN (EAN)	4050118034462	
Qty.	1 ST	
Type	ERTE ES HTI 15	Version
Order No.	1246370000	Pressing tool, Replacement part
GTIN (EAN)	4050118034462	
Qty.	1 ST	