

CUTFIX 8

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- For automatically cutting individual wires to length
- High repeat accuracy due to the precise servo DC drive
- Interface for controlling the automatic cutter via an IBM-compatible PC

General ordering data

Version	Cutting machine
Order No.	9023100000
Type	CUTFIX 8
GTIN (EAN)	4032248143184
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2025-01-06T00:00:00+01:00
Alternative product	CUTFIX PRO

CUTFIX 8

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	360 mm	Depth (inches)	14.1732 inch
Height	470 mm	Height (inches)	18.5039 inch
Width	385 mm	Width (inches)	15.1575 inch
Net weight	20289 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	d2df479e-2b79-4e98-adc7-b03577df98ae

Automatic cutting

Connected load	0.12 kW	Correction for length	Slip correction in mm can be programmed to suit the part.
Amount pre-selection, max.	Adjustable part quantity code	Drive	electrical
Storage	Up to 200 cutting orders	Keyboard	Entry and functions keypad
Feeding speed, max.	1.5 m/s	Indicator display	LCD display
Length pre-selection, max.	999999 mm	Length pre-selection, min.	1 mm
Interface	USB 1.1	Software	for data exchanging with IBM-compatible PC
Aperture (max. diameter)	8 mm outer diameter	Electrical connection	100 - 240 V AC / 50/60 Hz
Flexible/solid individual conductors	max. 10 mm ² / max. 2.5 mm ²		

Classifications

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		


CUTFIX 8

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Accessories / replacement parts



- For automatically cutting individual wires to length
- High repeat accuracy due to the precise servo DC drive
- Interface for controlling the automatic cutter via an IBM-compatible PC

General ordering data

Type	ATR CTF	Version
Order No.	1428560000	Accessories, Replacement part
GTIN (EAN)	4050118232899	
Qty.	1 ST	
Type	ATM CTF	Version
Order No.	1428570000	Automatic machines, Replacement part
GTIN (EAN)	4050118232790	
Qty.	1 ST	
Type	AIMESA V CUTFIX	Version
Order No.	9054740000	Accessories, Replacement part
GTIN (EAN)	4032248104512	
Qty.	1 ST	
Type	DOPPELZAHNRIEMEN VORSCH...	Version
Order No.	9054750000	Automatic machines, Replacement part
GTIN (EAN)	4032248104529	
Qty.	1 ST	
Type	ZAHNRIEMENVORSCHUBMOTC	Version
Order No.	9054760000	Automatic machines, Replacement part
GTIN (EAN)	4032248104536	
Qty.	1 ST	