

**H-BOX 4,0-16,0QMM DIN**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



Box filled with wire end ferrules with plastic collar:

- in Weidmüller colour code
- DIN colour code

**General ordering data**

Version	Assortment of wire end ferrules, Box, Colour code: DIN
Order No.	<a href="#">9025400000</a>
Type	H-BOX 4,0-16,0QMM DIN
GTIN (EAN)	4008 19034 1596
Qty.	1 items
Packaging	Box

## H-BOX 4,0-16,0QMM DIN

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Height	40 mm	Height (inches)	1.5748 inch
Diameter	92 mm	Net weight	68.64 g

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Technical data

Description of article	(2)Wire-end ferrule
------------------------	---------------------

### Wire-end ferrules

Colour code	DIN
-------------	-----

### Classifications

ETIM 8.0	EC000524	ETIM 9.0	EC000524
ETIM 10.0	EC000524	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

## H-BOX 4,0-16,0QMM DIN

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### packed loose in polythene bag



- supplied loose in polybag
- DIN colour code
- other colour code

### General ordering data

Type	H4,0/18D GR	Version	
Order No.	<a href="#">9019190000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, grey	
GTIN (EAN)	4008190141349		
Qty.	500 ST		

### Conductor nom. cross-section 6.0mm<sup>2</sup>



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

Type	H6,0/20D GE	Version	
Order No.	<a href="#">9019220000</a>	Wire-end ferrule, Standard, 14 mm, 12 mm, yellow	
GTIN (EAN)	4008190151607		
Qty.	100 ST		

### Conductor nom. cross-section 10mm<sup>2</sup>



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

Type	H10,0/22D R	Version	
Order No.	<a href="#">9019240000</a>	Wire-end ferrule, Standard, 15 mm, 12 mm, red	
GTIN (EAN)	4008190075385		
Qty.	100 ST		

## H-BOX 4,0-16,0QMM DIN

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Conductor nom. cross-section 16mm<sup>2</sup>



**16 mm<sup>2</sup>**

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

Type	H16,0/22D BL	Version	
Order No.	<a href="#">9019260000</a>	Wire-end ferrule, Standard, 15 mm, 12 mm, blue	
GTIN (EAN)	4008190125806		
Qty.	100 ST		