

H-BOX 4,0-16,0QMM DIN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Box filled with wire end ferrules with plastic collar:

- in Weidmüller colour code
- DIN colour code

General ordering data

Version	Assortment of wire end ferrules, Box, Colour code: DIN
Order No.	9025400000
Type	H-BOX 4,0-16,0QMM DIN
GTIN (EAN)	4008 19034 1596
Qty.	1 items
Packaging	Box

H-BOX 4,0-16,0QMM DIN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Height	40 mm	Height (inches)	1.5748 inch
Diameter	92 mm	Net weight	68.64 g

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article (2)Wire-end ferrule

Wire-end ferrules

Colour code DIN

Classifications

ETIM 8.0	EC000524	ETIM 9.0	EC000524
ETIM 10.0	EC000524	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

H-BOX 4,0-16,0QMM DIN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

packed loose in polythene bag




- supplied loose in polybag
- DIN colour code
- other colour code

General ordering data

Type	H4,0/18D GR	Version	
Order No.	9019190000	Wire-end ferrule, Standard, 12 mm, 10 mm, grey	
GTIN (EAN)	4008190141349		
Qty.	500 ST		

Conductor nom. cross-section 6.0mm²



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H6,0/20D GE	Version	
Order No.	9019220000	Wire-end ferrule, Standard, 14 mm, 12 mm, yellow	
GTIN (EAN)	4008190151607		
Qty.	100 ST		

Conductor nom. cross-section 10mm²



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H10,0/22D R	Version	
Order No.	9019240000	Wire-end ferrule, Standard, 15 mm, 12 mm, red	
GTIN (EAN)	4008190075385		
Qty.	100 ST		

H-BOX 4,0-16,0QMM DIN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Conductor nom. cross-section 16mm²



16 mm²

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H16,0/22D BL	Version	
Order No.	9019260000	Wire-end ferrule, Standard, 15 mm, 12 mm, blue	
GTIN (EAN)	4008190125806		
Qty.	100 ST		