

CRIMP-SET PZ 4 D

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimp sets

General ordering data

| | |
|------------|---------------------------------------------------------------------------------------------------------------------|
| Version | Assortment crimping tool, Crimping tool: PZ 4, Stripping tool: STRIPAX, Crimping range, min.: 0.5, Colour code: DIN |
| Order No. | 9028630000 |
| Type | CRIMP-SET PZ 4 D |
| GTIN (EAN) | 4032248392636 |
| Qty. | 1 items |
| Packaging | Plastic box |

CRIMP-SET PZ 4 D

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|--------------|
| Depth | 261 mm | Depth (inches) | 10.2756 inch |
| Height | 57 mm | Height (inches) | 2.2441 inch |
| Width | 338 mm | Width (inches) | 13.3071 inch |
| Net weight | 1752 g | | |

Environmental Product Compliance

| | |
|------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 1eacbb3e-7931-4ebb-9179-f29fd9b50028 |

Technical data

| | |
|------------------------|------------------------------------------------------------------------------------------------------------------|
| Description of article | Set includes crimping tool for up to 4 mm ² , stripping tool and wire-end ferrules in DIN colour code |
|------------------------|------------------------------------------------------------------------------------------------------------------|

Assortments

| | | | |
|----------------------|-------------------|----------------------|---------------------|
| Crimping range, max. | 4 mm ² | Crimping range, min. | 0.5 mm ² |
| Packaging | Plastic box | Stripping tool | STRIPAX |
| Crimping tool | PZ 4 | Colour code | DIN |
| Number of AEH | 3000 pcs. | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000524 | ETIM 9.0 | EC000524 |
| ETIM 10.0 | EC000524 | ECLASS 14.0 | 27-40-02-18 |
| ECLASS 15.0 | 27-40-02-18 | | |

CRIMP-SET PZ 4 D

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

| | | | |
|------------|----------------------------|-----------------------------------|--|
| Type | STRIPAX | Version | |
| Order No. | 9005000000 | Tools, Stripping and cutting tool | |
| GTIN (EAN) | 4008190072506 | | |
| Qty. | 1 ST | | |

Crimping tools



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

| | | | |
|------------|----------------------------|---------------------------------------------------------------------------------------------|--|
| Type | PZ 4 | Version | |
| Order No. | 9012500000 | Pressing tool, Crimping tool for wire-end ferrules, 0.5mm ² , 4mm ² , | |
| GTIN (EAN) | 4008190090920 | Trapezoidal crimp | |
| Qty. | 1 ST | | |

packed loose in polythene bag



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

CRIMP-SET PZ 4 D

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

General ordering data

| | | |
|------------|----------------------------|------------------------------------------------|
| Type | H0,5/14D W | Version |
| Order No. | 9019010000 | Wire-end ferrule, Standard, 10 mm, 8 mm, white |
| GTIN (EAN) | 4008190120931 | |
| Qty. | 500 ST | |
| Type | H0,75/14D GR | Version |
| Order No. | 9019040000 | Wire-end ferrule, Standard, 10 mm, 8 mm, grey |
| GTIN (EAN) | 4008190099077 | |
| Qty. | 500 ST | |
| Type | H1,0/14D R | Version |
| Order No. | 9019080000 | Wire-end ferrule, Standard, 10 mm, 8 mm, red |
| GTIN (EAN) | 4008190090623 | |
| Qty. | 500 ST | |
| Type | H1,5/14D SW | Version |
| Order No. | 9019120000 | Wire-end ferrule, Standard, 10 mm, 8 mm, black |
| GTIN (EAN) | 4008190153793 | |
| Qty. | 500 ST | |
| Type | H2,5/15D BL | Version |
| Order No. | 9019160000 | Wire-end ferrule, Standard, 10 mm, 8 mm, blue |
| GTIN (EAN) | 4008190028732 | |
| Qty. | 500 ST | |
| Type | H4,0/18D GR | Version |
| Order No. | 9019190000 | Wire-end ferrule, Standard, 12 mm, 10 mm, grey |
| GTIN (EAN) | 4008190141349 | |
| Qty. | 500 ST | |

Case



- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

General ordering data

| | | |
|------------|----------------------------|-----------------------|
| Type | KOFFER PSC4-01 | Version |
| Order No. | 9028860000 | Tools, Assortment box |
| GTIN (EAN) | 4032248304608 | |
| Qty. | 1 ST | |

CRIMP-SET PZ 4 D

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Inserts



- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

General ordering data

| | | | |
|------------|----------------------------|-----------------------|--|
| Type | EINSATZ A8-1 CL55 | Version | |
| Order No. | 9028460000 | Assortment of inserts | |
| GTIN (EAN) | 4032248310029 | | |
| Qty. | 100 ST | | |
| Type | EINSATZ A7-1 CL55 | Version | |
| Order No. | 9028450000 | Assortment of inserts | |
| GTIN (EAN) | 4032248310012 | | |
| Qty. | 1 ST | | |