

CRIMP-SET PZ 50

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimp sets

General ordering data

Version	Assortment crimping tool, Crimping tool: PZ 50, Stripping tool: AM 25, Crimping range, min.: 25, Colour code: Weidmüller
Order No.	9028850000
Type	CRIMP-SET PZ 50
GTIN (EAN)	403224838405 1
Qty.	1 items
Packaging	Plastic box

CRIMP-SET PZ 50

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	261 mm	Depth (inches)	10.2756 inch
Height	57 mm	Height (inches)	2.2441 inch
Width	338 mm	Width (inches)	13.3071 inch
Net weight	1759.55 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

Technical data

Description of article	Set includes crimping tool for up to 50 mm ² , stripping tool and wire-end ferrules in Weidmüller colour code
------------------------	--

Assortments

Crimping range, max.	50 mm ²	Crimping range, min.	25 mm ²
Packaging	Plastic box	Stripping tool	AM 25
Crimping tool	PZ 50	Colour code	Weidmüller
Number of AEH	200 pcs.		

Classifications

ETIM 8.0	EC000524	ETIM 9.0	EC000524
ETIM 10.0	EC000524	ECLASS 14.0	27-40-02-18
ECLASS 15.0	27-40-02-18		

CRIMP-SET PZ 50

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Tools



Sheathing stripper for PVC cables

General ordering data

Type	AM 25	Version	
Order No.	9001540000	Tools, Sheathing strippers	
GTIN (EAN)	4008190138271		
Qty.	1 ST		

Crimping tools



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Type	PZ 50	Version	
Order No.	9006450000	Pressing tool, Crimping tool for wire-end ferrules, 25mm ² , 50mm ² ,	
GTIN (EAN)	4008190095796	Indent crimp	
Qty.	1 ST		

Conductor nom. cross-section 35mm²



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

General ordering data

Type	H35,0/30D 16 R	Version	
Order No.	9019310000	Wire-end ferrule, Standard, 19 mm, 16 mm, red	
GTIN (EAN)	4008190102234		
Qty.	50 ST		

CRIMP-SET PZ 50

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Conductor nom. cross-section 50mm²

50 mm²

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

General ordering data

Type	H50,0/36D BL	Version	
Order No.	9019340000	Wire-end ferrule, Standard, 26 mm, 20 mm, blue	
GTIN (EAN)	4008190067632		
Qty.	50 ST		

Conductor nom. cross-section 25mm²

25 mm²

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H25,0/30T SW	Version	
Order No.	9021190000	Wire-end ferrule, Standard, 18 mm, 16 mm, black	
GTIN (EAN)	4008190115166		
Qty.	50 ST		
Type	H25,0/36T SW	Version	
Order No.	9021200000	Wire-end ferrule, Standard, 24 mm, 22 mm, black	
GTIN (EAN)	4008190055400		
Qty.	50 ST		