

## CRIMP-SET PZ 50

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Crimp sets

### General ordering data

Version	Assortment crimping tool, Crimping tool: PZ 50, Stripping tool: AM 25, Crimping range, min.: 25, Colour code: Weidmüller
Order No.	<a href="#">9028850000</a>
Type	CRIMP-SET PZ 50
GTIN (EAN)	403224838405 1
Qty.	1 items
Packaging	Plastic box

## CRIMP-SET PZ 50

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

Depth	261 mm	Depth (inches)	10.2756 inch
Height	57 mm	Height (inches)	2.2441 inch
Width	338 mm	Width (inches)	13.3071 inch
Net weight	1759.55 g		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

### Technical data

Description of article	Set includes crimping tool for up to 50 mm <sup>2</sup> , stripping tool and wire-end ferrules in Weidmüller colour code
------------------------	--

### Assortments

Crimping range, max.	50 mm <sup>2</sup>	Crimping range, min.	25 mm <sup>2</sup>
Packaging	Plastic box	Stripping tool	AM 25
Crimping tool	PZ 50	Colour code	Weidmüller
Number of AEH	200 pcs.		

### Classifications

ETIM 8.0	EC000524	ETIM 9.0	EC000524
ETIM 10.0	EC000524	ECLASS 14.0	27-40-02-18
ECLASS 15.0	27-40-02-18		

## CRIMP-SET PZ 50

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Tools



Sheathing stripper for PVC cables

#### General ordering data

Type	AM 25	Version	
Order No.	<a href="#">9001540000</a>	Tools, Sheathing strippers	
GTIN (EAN)	4008190138271		
Qty.	1 ST		

### Crimping tools



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

#### General ordering data

Type	PZ 50	Version	
Order No.	<a href="#">9006450000</a>	Pressing tool, Crimping tool for wire-end ferrules, 25mm <sup>2</sup> , 50mm <sup>2</sup> ,	
GTIN (EAN)	4008190095796	Indent crimp	
Qty.	1 ST		

### Conductor nom. cross-section 35mm<sup>2</sup>



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

#### General ordering data

Type	H35,0/30D 16 R	Version	
Order No.	<a href="#">9019310000</a>	Wire-end ferrule, Standard, 19 mm, 16 mm, red	
GTIN (EAN)	4008190102234		
Qty.	50 ST		


**CRIMP-SET PZ 50**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Accessories**

**Conductor nom. cross-section 50mm<sup>2</sup>**



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

**General ordering data**

Type	H50,0/36D BL	Version	
Order No.	<a href="#">9019340000</a>	Wire-end ferrule, Standard, 26 mm, 20 mm, blue	
GTIN (EAN)	4008190067632		
Qty.	50 ST		

**Conductor nom. cross-section 25mm<sup>2</sup>**



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

**General ordering data**

Type	H25,0/30T SW	Version	
Order No.	<a href="#">9021190000</a>	Wire-end ferrule, Standard, 18 mm, 16 mm, black	
GTIN (EAN)	4008190115166		
Qty.	50 ST		
Type	H25,0/36T SW	Version	
Order No.	<a href="#">9021200000</a>	Wire-end ferrule, Standard, 24 mm, 22 mm, black	
GTIN (EAN)	4008190055400		
Qty.	50 ST		