

**DMS 3 SET 2 ZERT**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

**General ordering data**

Version	DMS 3, Mains-operated torque screwdriver
Order No.	<a href="#">9017420000</a>
Type	DMS 3 SET 2 ZERT
GTIN (EAN)	4008190856564
Qty.	1 items

## DMS 3 SET 2 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Depth	205 mm	Depth (inches)	8.0709 inch
Width	325 mm	Width (inches)	12.7952 inch
Net weight	1920 g		

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	8a39b146-a7e9-4fe1-a2bc-f82c0bb3aeeb

### Technical data

Description of article	Cordless torque screwdriver set, as set 1 but with additional rechargeable battery
------------------------	--

### Electric screwdriver

Idling speed	200 u. 400 min <sup>-1</sup>	Weight	2004 g
Nominal voltage	2.4 V	Bit holder	1/4" DIN 3126 Form E6.3
Torque setting, max.	3 Nm	Torque setting, min.	0.3 Nm
Rechargeable batteries	Ni-Mh cells	Weight of rechargeable battery	122 g

### Screwing tools

Torque setting, max.	3 Nm	Torque setting, min.	0.3 Nm
----------------------	------	----------------------	--------

### Classifications

ETIM 8.0	EC001395	ETIM 9.0	EC001395
ETIM 10.0	EC001395	ECLASS 14.0	21-05-08-90
ECLASS 15.0	21-05-08-90		

**DMS 3 SET 2 ZERT**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

**Example of use**

