

CRIMP-SET PZ 16

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimp sets

General ordering data

Version	Assortment crimping tool, Crimping tool: PZ 16, Stripping tool: STRIPAX 16, Crimping range, min.: 6, Colour code: Weidmüller
Order No.	9025850000
Type	CRIMP-SET PZ 16
GTIN (EAN)	4008190184520
Qty.	1 items
Packaging	Plastic box

CRIMP-SET PZ 16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	261 mm	Depth (inches)	10.2756 inch
Height	57 mm	Height (inches)	2.2441 inch
Width	338 mm	Width (inches)	13.3071 inch
Net weight	1680.74 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

Technical data

Description of article	Set includes crimping tool for up to 16 mm ² , stripping tool and wire-end ferrules in Weidmüller colour code
------------------------	--

Assortments

Crimping range, max.	16 mm ²	Crimping range, min.	6 mm ²
Packaging	Plastic box	Stripping tool	STRIPAX 16
Crimping tool	PZ 16	Colour code	Weidmüller
Number of AEH	400 pcs.		

Classifications

ETIM 8.0	EC000524	ETIM 9.0	EC000524
ETIM 10.0	EC000524	ECLASS 14.0	27-40-02-18
ECLASS 15.0	27-40-02-18		

CRIMP-SET PZ 16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Conductor nom. cross-section 6.0mm²

6 mm²

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H6,0/20 SW	Version	
Order No.	0533500000	Wire-end ferrule, Standard, 14 mm, 12 mm, black	
GTIN (EAN)	4008190183905		
Qty.	100 ST		

Conductor nom. cross-section 10mm²

10 mm²

- supplied loose in polybag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H10,0/22 EB	Version	
Order No.	0534200000	Wire-end ferrule, Standard, 15 mm, 12 mm, Ivory	
GTIN (EAN)	4008190033460		
Qty.	100 ST		

Conductor nom. cross-section 16mm²

16 mm²

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H16,0/22 GN	Version	
Order No.	0565900000	Wire-end ferrule, Standard, 15 mm, 12 mm, green	
GTIN (EAN)	4008190022181		
Qty.	100 ST		

CRIMP-SET PZ 16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	H16,0/28 GN	Version	
Order No.	0566000000	Wire-end ferrule, Standard, 21 mm, 18 mm, green	
GTIN (EAN)	4008190165406		
Qty.	100 ST		

Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Type	STRIPAX	Version	
Order No.	9005000000	Tools, Stripping and cutting tool	
GTIN (EAN)	4008190072506		
Qty.	1 ST		

Crimping tools



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Type	PZ 16	Version	
Order No.	9012600000	Pressing tool, Crimping tool for wire-end ferrules, 6mm ² , 16mm ² , Indent crimp	
GTIN (EAN)	4008190035440		
Qty.	1 ST		

CRIMP-SET PZ 16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Case



- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

General ordering data

Type	KOFFER PSC4-01	Version	
Order No.	9028860000	Tools, Assortment box	
GTIN (EAN)	4032248304608		
Qty.	1 ST		

Inserts



- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

General ordering data

Type	EINSATZ A8-1 CL55	Version	
Order No.	9028460000	Assortment of inserts	
GTIN (EAN)	4032248310029		
Qty.	100 ST		
Type	EINSATZ A7-1 CL55	Version	
Order No.	9028450000	Assortment of inserts	
GTIN (EAN)	4032248310012		
Qty.	1 ST		