

**CRIMP-SET STRIPAX PLUS T**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Crimp sets

**General ordering data**

Version	Assortment crimping tool, Crimping tool: STRIPAX-Plus, Stripping tool: STRIPAX-Plus, Crimping range, min.: 0.5, Colour code: Miscellaneous
Order No.	<a href="#">9028790000</a>
Type	CRIMP-SET STRIPAX PLUS T
GTIN (EAN)	4032248392773
Qty.	1 items

## CRIMP-SET STRIPAX PLUS T

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

Depth	261 mm	Depth (inches)	10.2756 inch
Height	57 mm	Height (inches)	2.2441 inch
Width	338 mm	Width (inches)	13.3071 inch
Net weight	1101.61 g		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

### Assortments

Crimping range, max.	2.5 mm <sup>2</sup>	Crimping range, min.	0.5 mm <sup>2</sup>
Stripping tool	STRIPAX-Plus	Crimping tool	STRIPAX-Plus
Colour code	Miscellaneous	Number of AEH	2500 pcs.

### Classifications

ETIM 8.0	EC000524	ETIM 9.0	EC000524
ETIM 10.0	EC000524	ECLASS 14.0	27-40-02-18
ECLASS 15.0	27-40-02-18		

## CRIMP-SET STRIPAX PLUS T

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Strip of wire end ferrules



- Linked of wire-end ferrule strips (50 pcs.)
- Weidmüller colour code
- DIN colour code

### General ordering data

Type	H0,5/14D W BD	Version
Order No.	<a href="#">9004280000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, white
GTIN (EAN)	4008190162627	
Qty.	500 ST	
Type	H0,75/14T HBL BD	Version
Order No.	<a href="#">9004310000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, Light Blue
GTIN (EAN)	4008190179298	
Qty.	500 ST	
Type	H1,0/14D R BD	Version
Order No.	<a href="#">9004330000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, red
GTIN (EAN)	4008190047498	
Qty.	500 ST	
Type	H1,5/14D SW BD	Version
Order No.	<a href="#">9004350000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, black
GTIN (EAN)	4008190005474	
Qty.	500 ST	
Type	H2,5/14T GR BD	Version
Order No.	<a href="#">9004370000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, grey
GTIN (EAN)	4008190052508	
Qty.	500 ST	

### Stripax plus



Cutting, stripping and crimping tools for connected wire-end ferrules strips

- Cutting
- Stripping
- Crimping
- Automatic feeding of wire end ferrules
- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- Efficient: only one tool needed for cable work, and thus significant time saved
- Only strips of linked wire end ferrules, each containing 50 pieces, from Weidmüller may be processed. The use of wire end ferrules on reels may lead to destructon.

### General ordering data

Type	STRIPAX PLUS 2.5	Version
Order No.	<a href="#">9020000000</a>	Cutting, stripping and crimping tool, Crimping tool for wire-end ferrules, 0.5mm <sup>2</sup> , 2.5mm <sup>2</sup> , Trapezoidal crimp
GTIN (EAN)	4008190067267	
Qty.	1 ST	

## CRIMP-SET STRIPAX PLUS T

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Case



- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

### General ordering data

Type	KOFFER PSC4-01	Version	
Order No.	<a href="#">9028860000</a>	Tools, Assortment box	
GTIN (EAN)	4032248304608		
Qty.	1 ST		