

MULTI-STRIPAX 6-16

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- For flexible and solid conductors with special insulating materials
- High-quality stripping for industrial applications (complies with aircraft industry requirements)
- Specially shaped blades enable stripping of special types of insulation and conductor configurations
- Stripping length adjustable via end stop
- Very versatile thanks to interchangeable stripping units
- Stripping results reproduced accurately over and over again
- No damage to the conductor
- A long-lasting, reliable tool thanks to its sturdy design
- Integrated cutting function

General ordering data

Version	Tools, Stripping and cutting tool
Order No.	9202210000
Type	MULTI-STRIPAX 6-16
GTIN (EAN)	4032248486144
Qty.	1 items

MULTI-STRIPAX 6-16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	40 mm	Depth (inches)	1.5748 inch
Height	85 mm	Height (inches)	3.3464 inch
Width	250 mm	Width (inches)	9.8425 inch
Net weight	509.1 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Technical data

Description of article	Stripping and cutting tool for 6, 10 and 16 mm ² ; PVC-insulated conductors with special configurations
------------------------	--

Stripping tools

Cable type	Flexible and solid conductors with PVC insulation	Conductor cross-section (cutting capacity)	6 mm ²
max. cutting capacity, solid	2.5 mm ²	max. cutting capacity, fine-strand	6 mm ²
max. cutting capacity, ribbon	10,2 mm x 4 mm	Stripping range AWG, max.	6 AWG
Stripping range AWG, min.	10 AWG	Stripping length, min.	2 mm
Conductor cross-section, max.	16 mm ²	Conductor cross-section, min.	6 mm ²

Classifications

ETIM 8.0	EC002109	ETIM 9.0	EC002109
ETIM 10.0	EC002109	ECLASS 14.0	21-04-37-06
ECLASS 15.0	21-04-37-06		

MULTI-STRIPAX 6-16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Accessories / replacement parts



- For flexible and solid conductors with special insulating materials
- High-quality stripping for industrial applications (complies with aircraft industry requirements)
- Specially shaped blades enable stripping of special types of insulation and conductor configurations
- Stripping length adjustable via end stop
- Very versatile thanks to interchangeable stripping units
- Stripping results reproduced accurately over and over again
- No damage to the conductor
- A long-lasting, reliable tool thanks to its sturdy design
- Integrated cutting function

General ordering data

Type	AIE M-SPX 0.25-1.5 S	Version
Order No.	9204550000	Insert
GTIN (EAN)	4032248671090	
Qty.	1 ST	
Type	AIE M-SPX 1.5-6.0 S	Version
Order No.	9204570000	Insert
GTIN (EAN)	4032248671113	
Qty.	1 ST	
Type	AIE MULTI-SPX 0.75-4 ² SL	Version
Order No.	9203730000	Insert
GTIN (EAN)	4032248576449	
Qty.	1 ST	
Type	AIE MULTI-STRIPAX 16 SL	Version
Order No.	9202270000	Insert
GTIN (EAN)	4032248486212	
Qty.	1 ST	
Type	AIE MULTI-STRIPAX 6-16	Version
Order No.	9202260000	Insert
GTIN (EAN)	4032248486205	
Qty.	1 ST	
Type	AIE MULTI-STRIPAX ASI	Version
Order No.	9202300000	Insert
GTIN (EAN)	4032248486250	
Qty.	1 ST	
Type	AIE MULTI-STRIPAX AWG	Version
Order No.	9202280000	Insert
GTIN (EAN)	4032248486236	
Qty.	1 ST	
Type	AIE MULTI-STRIPAX GKWLW	Version
Order No.	9205770000	Insert
GTIN (EAN)	4032248836291	
Qty.	1 ST	
Type	AIE MULTI-STRIPAX POF	Version
Order No.	1212770000	Insert
GTIN (EAN)	4032248994434	
Qty.	1 ST	

MULTI-STRIPAX 6-16

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Type	AIE MULTI-STRIPAX PV	Version
Order No.	1204280000	Insert
GTIN (EAN)	4032248987030	
Qty.	1 ST	
Type	ERAN MULTI-STRIPAX	Version
Order No.	9203100000	Spare stop set
GTIN (EAN)	4032248538102	
Qty.	1 ST	
Type	ERME MULTI-STRIPAX	Version
Order No.	9203070000	Spare cutting blade
GTIN (EAN)	4032248538096	
Qty.	1 ST	