

PRO CASE PREMIUM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

General ordering data

| | |
|------------|----------------------------|
| Version | Tool case with contents |
| Order No. | 9202460000 |
| Type | PRO CASE PREMIUM |
| GTIN (EAN) | 4032248493425 |
| Qty. | 1 items |
| Packaging | Case |

PRO CASE PREMIUM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|--------------|
| Depth | 170 mm | Depth (inches) | 6.6929 inch |
| Height | 400 mm | Height (inches) | 15.748 inch |
| Width | 480 mm | Width (inches) | 18.8976 inch |
| Net weight | 6179 g | | |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 7a, 7cl |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 1eacbb3e-7931-4ebb-9179-f29fd9b50028 |

Technical data

| | |
|------------------------|-----------|
| Description of article | Tool case |
|------------------------|-----------|

Assortments

| | |
|-----------|------|
| Packaging | Case |
|-----------|------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000149 | ETIM 9.0 | EC000149 |
| ETIM 10.0 | EC000149 | ECLASS 14.0 | 21-04-50-03 |
| ECLASS 15.0 | 21-04-50-03 | | |

PRO CASE PREMIUM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



PRO CASE PREMIUM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Empty



Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

General ordering data

| | | | |
|------------|----------------------------|----------------|--|
| Type | PRO CASE LEER | Version | |
| Order No. | 9202470000 | Assortment box | |
| GTIN (EAN) | 4032248495788 | | |
| Qty. | 1 ST | | |

Tools



Sheathing stripper for PVC cables

General ordering data

| | | | |
|------------|----------------------------|----------------------------|--|
| Type | AM 25 | Version | |
| Order No. | 9001540000 | Tools, Sheathing strippers | |
| GTIN (EAN) | 4008190138271 | | |
| Qty. | 1 ST | | |

Cutting tools



Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | KT 8 | Version | |
| Order No. | 9002650000 | Cutting tools, Cutting tool for one-hand operation | |
| GTIN (EAN) | 4008190020163 | | |
| Qty. | 1 ST | | |

PRO CASE PREMIUM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

| | | | |
|------------|----------------------------|-----------------------------------|--|
| Type | STRIPAX | Version | |
| Order No. | 9005000000 | Tools, Stripping and cutting tool | |
| GTIN (EAN) | 4008190072506 | | |
| Qty. | 1 ST | | |

Crimping tools



- Crimping tools for wire end ferrules, with and without plastic collars
- Ratchet guarantees precise crimping
 - Release option in the event of incorrect operation

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | PZ 6 ROTO L | Version | |
| Order No. | 1444050000 | Pressing tool, Crimping tool for wire-end ferrules, 0.14mm ² , 6mm ² , | |
| GTIN (EAN) | 4050118248593 | Trapezoidal crimp | |
| Qty. | 1 ST | | |

Assortment of wire end ferrules with plastic collar



- Box filled with wire end ferrules with plastic collar:
- in Weidmüller colour code
 - DIN colour code

PRO CASE PREMIUM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | H-BOX 0,5-2,5QMM DIN | Version | |
| Order No. | 9025430000 | Assortment of wire end ferrules, Box, Colour code: DIN | |
| GTIN (EAN) | 4008190337162 | | |
| Qty. | 1 ST | | |

Tools



Sheathing stripper for PVC cables

General ordering data

| | | | |
|------------|----------------------------|----------------------------|--|
| Type | AM 12 | Version | |
| Order No. | 9030060000 | Tools, Sheathing strippers | |
| GTIN (EAN) | 4008190337827 | | |
| Qty. | 1 ST | | |

with LCD Display



The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LCD-Display
- acc. to VDE standard,
- high peak voltage strength
- the right tester for every application

General ordering data

| | | | |
|------------|----------------------------|--------------------------------------|--|
| Type | VT DIGI PRO | Version | |
| Order No. | 9918870000 | Testing tools, 2-pole voltage tester | |
| GTIN (EAN) | 4032248405756 | | |
| Qty. | 1 ST | | |

PRO CASE PREMIUM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

with LED Display



The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LED-Display
- acc. to VDE standard
- high peak voltage strength
- the right tester for every application

General ordering data

| | | | |
|------------|----------------------------|--------------------------------------|--|
| Type | VT COMBI PRO | Version | |
| Order No. | 9918860000 | Testing tools, 2-pole voltage tester | |
| GTIN (EAN) | 4032248405749 | | |
| Qty. | 1 ST | | |

Tools



- For fast and accurate stripping of cables for damp areas ranging from 8 - 13 mm diameter, e.g. NYM cable, 3 x 1.5 mm² to 5 x 2.5 mm²
- No need to set cutting depth
- Ideal for working in junction and distribution boxes

General ordering data

| | | | |
|------------|----------------------------|---------------------|--|
| Type | STRIPPER ROUND TOP | Version | |
| Order No. | 9918050000 | Sheathing strippers | |
| GTIN (EAN) | 4032248359165 | | |
| Qty. | 1 ST | | |

VDE insulated telephone pliers



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

PRO CASE PREMIUM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | FRZ S 160 | Version | |
| Order No. | 9046370000 | Pliers | |
| GTIN (EAN) | 4032248357673 | | |
| Qty. | 1 ST | | |

VDE-insulated diagonal-cutting pliers



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

General ordering data

| | | | |
|------------|----------------------------|-------------------------|--|
| Type | SE HD 180 | Version | |
| Order No. | 9046330000 | Diagonal-cutting pliers | |
| GTIN (EAN) | 4032248357635 | | |
| Qty. | 1 ST | | |

VDE-insulated combination pliers



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | KBZ 180 | Version | |
| Order No. | 9046290000 | Pliers | |
| GTIN (EAN) | 4032248356485 | | |
| Qty. | 1 ST | | |

PRO CASE PREMIUM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

VDE-insulated flat- and round-nose pliers



- up to 1000 V (AC) and 1500 V (DC)
 protective insulation acc. to IEC 900. DIN EN 60900
- drop-forged from high-quality special tool steels
 - safety handle with ergonomic and non-slip TPE VDE sleeve
 - Made from shockproof, heat-and cold-resistant, non-flammable, cadmium-free TPE (thermoplastic elastomer)
 - Elastic grip zone and hard core
 - Highly-polished surface
 - nickel-chromium electro-galvanised coating protects against corrosion

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | RZ 160 | Version | |
| Order No. | 9046360000 | Pliers | |
| GTIN (EAN) | 4032248357666 | | |
| Qty. | 1 ST | | |

VDE insulated special function pliers



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose. Weidmüller offers a complete line of pliers which comply with national and international testing standards. All pliers are produced and tested according to DIN EN 60900. The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | AIZ 160 | Version | |
| Order No. | 9046440000 | Pliers | |
| GTIN (EAN) | 4032248357772 | | |
| Qty. | 1 ST | | |

Cabinet keys



Crimped conductors are fixed in their respective wiring spaces by screws or a direct plug-in feature. Weidmüller can supply a wide range of tools for screwing.

PRO CASE PREMIUM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

General ordering data

| | | | |
|------------|----------------------------|---------------|--|
| Type | CROSS-KEY UNIVERSAL | Version | |
| Order No. | 9918130000 | Universal key | |
| GTIN (EAN) | 4032248371112 | | |
| Qty. | 1 ST | | |

Combined screwing and cutting tool "Swifty® CS"

Combined cutting/stripping tool Swifty® CS and Swifty® CS set for crimp-free cutting and stripping of copper cables up to 1.5 mm² solid and 2.5 mm² flexible.

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | SWIFTY CS SET | Version | |
| Order No. | 9006060000 | Cutting and screwing-tool, Cutting tool for one-hand operation | |
| GTIN (EAN) | 4032248257638 | | |
| Qty. | 1 ST | | |

Socket wrench sets

Allen key made from fully hardened, high-alloy chromium-vanadium- steel, acc. to DIN ISO 2936 L (DIN 911), high-quality refined surface.



General ordering data

| | | | |
|------------|----------------------------|-----------------|--|
| Type | SK WSD-S 1,5-10,0 | Version | |
| Order No. | 9008850000 | Mounting tool | |
| GTIN (EAN) | 4032248266609 | | |
| Qty. | 1 ST | | |
| Type | SKS 2,0-8,0 MR | Version | |
| Order No. | 9008870000 | socket wrenches | |
| GTIN (EAN) | 4032248266623 | | |
| Qty. | 1 ST | | |

PRO CASE PREMIUM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

Torque screwdriver



If you demand effective and exact work, it is essential to use the precise torque. This also guarantees high repetition accuracy.

This is the perfect job for the new Weidmüller torque screwdriver with the ergonomic grip and the unique interchangeable bit system.

- Compact and especially light design
- Torque set with special tool (supplied); an unintended, incorrect setting is ruled out.
- Ergonomic handle sizes matched to the torque range.
- Tools subjected to routine testing and provided with an ID number; 100% quality control with verification and product reference.
- Clicking sound upon reaching the set torque, clearly audible and noticeable, no unnecessary tightening.
- Interchangeable blades made from high-quality wear-resistant tool steel.
- All tools fulfil the accuracy requirements of: EN ISO 6798, BS EN 26789, ASME B107.14M
- Trigger accuracy +/- 6% of the set scale value.

General ordering data

| | | | |
|------------|----------------------------|--------------------|--|
| Type | DMS MANUELL 0,5-1,7 | Version | |
| Order No. | 9918370000 | Torque screwdriver | |
| GTIN (EAN) | 4032248388332 | | |
| Qty. | 1 ST | | |

Screwdriver Sets



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

| | | | |
|------------|----------------------------|---------------|--|
| Type | SDI SET SLIM S3.5-6.5/P... | Version | |
| Order No. | 2749580000 | Mounting tool | |
| GTIN (EAN) | 4050118896329 | | |
| Qty. | 1 ST | | |

PRO CASE PREMIUM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Set of non-insulated screwdrivers



Weidmüller SoftFinish screwdriver for general uses, blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, matt chrome finish.

General ordering data

| | | | |
|------------|----------------------------|-----------------|--|
| Type | SD SET S2.5-5.5/PH1/2 | Version | |
| Order No. | 2749200000 | Screwdriver set | |
| GTIN (EAN) | 4050118895506 | | |
| Qty. | 1 ST | | |

Bit assortment, E6.3



1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection

General ordering data

| | | | |
|------------|----------------------------|---------------|--|
| Type | BIT-BOX 11 | Version | |
| Order No. | 2748110000 | Mounting tool | |
| GTIN (EAN) | 4050118894493 | | |
| Qty. | 1 ST | | |