

CRIMPSET PZ / CTI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimp sets

General ordering data

Version	Assortment crimping tool, Crimping tool: PZ 6 Roto/CTI 6, Stripping tool: STRIPAX, Crimping range, min.: 0.14, Colour code: DIN
Order No.	9202610000
Type	CRIMPSET PZ / CTI
GTIN (EAN)	4032248502776
Qty.	1 items
Packaging	Plastic box

CRIMPSET PZ / CTI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	330 mm	Depth (inches)	12.9921 inch
Height	79 mm	Height (inches)	3.1102 inch
Width	413 mm	Width (inches)	16.2598 inch
Net weight	4871.4 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

Assortments

Crimping range, max.	6 mm ²	Crimping range, min.	0.14 mm ²
Packaging	Plastic box	Stripping tool	STRIPAX
Crimping tool	PZ 6 Roto/CTI 6	Colour code	DIN
Number of AEH	2000 pcs.		

Classifications

ETIM 8.0	EC000524	ETIM 9.0	EC000524
ETIM 10.0	EC000524	ECLASS 14.0	27-40-02-18
ECLASS 15.0	27-40-02-18		

CRIMPSET PZ / CTI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Type	STRIPAX	Version	
Order No.	9005000000	Tools, Stripping and cutting tool	
GTIN (EAN)	4008190072506		
Qty.	1 ST		

Crimping tools



- Crimping tools for insulated connectors cable lugs, terminal pins, parallel and serial connectors, plug-in connectors
- Ratchet guarantees precise crimping
 - Release option in the event of incorrect operation
 - With stop for exact positioning of the contacts.
 - Tested to DIN EN 60352 part 2

General ordering data

Type	CTI 6	Version	
Order No.	9006120000	Pressing tool, Crimping tool for contacts, 0.5mm ² , 6mm ² , Oval crimping, Double crimp	
GTIN (EAN)	4008190044527		
Qty.	1 ST		
Type	PZ 6 ROTO L	Version	
Order No.	1444050000	Pressing tool, Crimping tool for wire-end ferrules, 0.14mm ² , 6mm ² , Trapezoidal crimp	
GTIN (EAN)	4050118248593		
Qty.	1 ST		

CRIMPSET PZ / CTI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

packed loose in polythene bag



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

General ordering data

Type	H0,5/14D W	Version	
Order No.	9019010000	Wire-end ferrule, Standard, 10 mm, 8 mm, white	
GTIN (EAN)	4008190120931		
Qty.	500 ST		
Type	H1,0/14D R	Version	
Order No.	9019080000	Wire-end ferrule, Standard, 10 mm, 8 mm, red	
GTIN (EAN)	4008190090623		
Qty.	500 ST		
Type	H2,5/15D BL	Version	
Order No.	9019160000	Wire-end ferrule, Standard, 10 mm, 8 mm, blue	
GTIN (EAN)	4008190028732		
Qty.	500 ST		
Type	H4,0/18D GR	Version	
Order No.	9019190000	Wire-end ferrule, Standard, 12 mm, 10 mm, grey	
GTIN (EAN)	4008190141349		
Qty.	500 ST		

Conductor nom. cross-section 6.0mm²

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H6,0/20D GE	Version	
Order No.	9019220000	Wire-end ferrule, Standard, 14 mm, 12 mm, yellow	
GTIN (EAN)	4008190151607		
Qty.	100 ST		


CRIMPSET PZ / CTI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Ring cable lugs



Insulated ring-cable connector made from PVC

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Type	LIR 6M6 V	Version	
Order No.	9200250000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6	
GTIN (EAN)	4032248410071	mm ²	
Qty.	100 ST		

Pin cable lugs




Insulated pin-cable connector made from PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel

General ordering data

Type	LIP 6R14 V	Version	
Order No.	9200480000	cable lug, terminal end, Insulated cable connector, 4 mm ² - 6	
GTIN (EAN)	4032248410323	mm ² , yellow	
Qty.	100 ST		

Ring cable lugs



Insulated ring-cable connector made from PVC

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Type	LIR 2,5M5 V	Version	
Order No.	9200180000	cable lug, terminal end, Insulated cable connector, 2,5 mm ² , 1,5 mm ² -	
GTIN (EAN)	4032248409808	2,5 mm ²	
Qty.	100 ST		

CRIMPSET PZ / CTI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Cable-lug sleeves



Insulated tab-connector sleeves made from PVC with copper sleeve

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Type	LIF 2,5F638 R	Version	
Order No.	9200560000		cable lug, terminal end, Insulated cable connector, 2,5 mm ² , 1,5 mm ² -
GTIN (EAN)	4032248410408		2.5 mm ² , blue
Qty.	100 ST		

Pin cable lugs



Insulated pin-cable connector made from PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel

General ordering data

Type	LIP 1,5R12 V	Version	
Order No.	9200460000		cable lug, terminal end, Insulated cable connector, 0,5 mm ² - 1,5
GTIN (EAN)	4032248410309		mm ² , red
Qty.	100 ST		
Type	LIP 2,5R12 V	Version	
Order No.	9200470000		cable lug, terminal end, Insulated cable connector, 1,5 mm ² - 2,5
GTIN (EAN)	4032248410316		mm ² , blue
Qty.	100 ST		

Joint connector



Fully-insulated joint connector made from PVC or PC/PA

- Conventional designs
- Not soldered

CRIMPSET PZ / CTI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany


www.weidmueller.com

Accessories

General ordering data

Type	LIB 6B26 VF	Version	
Order No.	9200510000		cable lug, terminal end, Insulated cable connector, 4 mm ² - 6 mm ² , yellow
GTIN (EAN)	4032248410354		
Qty.	100 ST		

Ring cable lugs




Insulated ring-cable connector made from PVC

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Type	LIR 1,5M4 V	Version	
Order No.	9200090000		cable lug, terminal end, Insulated cable connector, 1.5 mm ² , 0.5 mm ² - 1.5 mm ²
GTIN (EAN)	4032248409853		
Qty.	100 ST		

Cable-lug sleeves



Insulated tab-connector sleeves made from PVC with copper sleeve

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Type	LIF 1,5F638 R	Version	
Order No.	9200540000		cable lug, terminal end, Insulated cable connector, 1.5 mm ² , 0.5 mm ² - 1.5 mm ² , red
GTIN (EAN)	4032248410385		
Qty.	100 ST		

CRIMPSET PZ / CTI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Joint connector




Fully-insulated joint connector made from PVC or PC/PA

- Conventional designs
- Not soldered

General ordering data

Type	LIB 2,5B25 VF	Version	
Order No.	9200500000		cable lug, terminal end, Insulated cable connector, 1,5 mm ² - 2,5 mm ² , blue
GTIN (EAN)	4032248410347		
Qty.	100 ST		

Ring cable lugs



Insulated ring-cable connector made from PVC

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Type	LIR 1,5M5 V	Version	
Order No.	9200100000		cable lug, terminal end, Insulated cable connector, 1,5 mm ² , 0,5 mm ² - 1,5 mm ²
GTIN (EAN)	4032248409860		
Qty.	100 ST		

Inserts



- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

General ordering data

Type	EINSATZ BA8-PSC 80	Version	
Order No.	9202310000		Assortment of inserts
GTIN (EAN)	4032248486687		
Qty.	1 ST		

CRIMPSET PZ / CTI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Cable-lug sleeves



Insulated tab-connector sleeves made from PVC with copper sleeve

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Type	LIF 1,5F288 R	Version	
Order No.	9200520000		cable lug, terminal end, Insulated cable connector, 1,5 mm ² , 0,5 mm ² -
GTIN (EAN)	4032248410361		1,5 mm ² , red
Qty.	100 ST		
Type	LIF 6F638 R	Version	
Order No.	9200570000		cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6
GTIN (EAN)	4032248410415		mm ² , yellow
Qty.	100 ST		

Joint connector



Fully-insulated joint connector made from PVC or PC/PA

- Conventional designs
- Not soldered

General ordering data

Type	LIB 1,5B25 VF	Version	
Order No.	9200490000		cable lug, terminal end, Insulated cable connector, 0,5 mm ² - 1,5
GTIN (EAN)	4032248410330		mm ² , red
Qty.	100 ST		

Case



- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

CRIMPSET PZ / CTI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

General ordering data

Type	KOFFER PSC80 PC	Version	
Order No.	9202330000	Tools, Empty box / Case	
GTIN (EAN)	4032248486700		
Qty.	1 ST		