


LIF 2,5F638 RF

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Fully-insulated tab-connector sleeves made from PVC with copper sleeve

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

| | |
|------------|--|
| Version | cable lug, terminal end, Insulated cable connector, 1.5 mm ² - 2.5 mm ² , blue |
| Order No. | 9200650000 |
| Type | LIF 2,5F638 RF |
| GTIN (EAN) | 40322484 1049 1 |
| Qty. | 100 items |

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|----------------|-------------|
| Depth | 6.3 mm | Depth (inches) | 0.248 inch |
| Width | 22 mm | Width (inches) | 0.8661 inch |
| Net weight | 1.25 g | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Technical data

| | |
|------------------------|---|
| Description of article | Fully-insulated tab-connector sleeves 1.5-2.5 mm ² |
|------------------------|---|


Connectors

| | | | |
|-------------------------------|---------------------|----------------------------------|---------------------|
| Conductor cross-section, max. | 2.5 mm ² | Conductor cross-section, min. | 1.5 mm ² |
| Insulation | Fully insulated | Dimension (flat blade connector) | 6.3 x 0.8 mm |
| Dimension | 6.3 x 0.8 mm | Material/plastic | PVC |
| Identification colour | blue | Plug-in width (d2) | 6.3 mm |
| Plug-in density (d3) | 0.8 mm | Plastic collar length (b) | 10.5 mm |
| Plastic collar diameter (D) | 5 mm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC0005 16 | ETIM 9.0 | EC0005 16 |
| ETIM 10.0 | EC0005 16 | ECLASS 14.0 | 27-44-03-92 |
| ECLASS 15.0 | 27-44-03-92 | | |

Drawings



LIF 2,5F638 RF

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Crimping tools



Crimping tools for insulated connectors
cable lugs, terminal pins, parallel and serial connectors,
plug-in connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.
- Tested to DIN EN 60352 part 2

General ordering data

| | | |
|------------|----------------------------|---|
| Type | HTI 15 | Version |
| Order No. | 9014400000 | Pressing tool, Tool for insulated cable connectors, 0.5mm ² , 2.5mm ² , |
| GTIN (EAN) | 4008190159412 | Double crimp |
| Qty. | 1 ST | |
| Type | CTI 6 | Version |
| Order No. | 9006120000 | Pressing tool, Crimping tool for contacts, 0.5mm ² , 6mm ² , Oval |
| GTIN (EAN) | 4008190044527 | crimping, Double crimp |
| Qty. | 1 ST | |
| Type | CTI 6 G | Version |
| Order No. | 9202850000 | Pressing tool, Tool for insulated cable connectors, 0.5mm ² , 6mm ² , |
| GTIN (EAN) | 4032248517855 | Oval crimping, Parallel crimp |
| Qty. | 1 ST | |