

KT 55**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Cutting tools in mechanical ratchet version. Suitable for non-pinch cutting of copper and aluminium conductors. Easy operation thanks to optimum leverage and a cleverly engineered cam mechanism.

General ordering data

| | |
|---------------------|---------------------------------------------------------|
| Version | Cutting tools, Circular cable cutter |
| Order No. | 9202060000 |
| Type | KT 55 |
| GTIN (EAN) | 4032248482191 |
| Qty. | 1 items |
| Delivery status | This article will no longer be available in the future. |
| Available until | 2024-10-28T00:00:00+01:00 |
| Alternative product | KT 50 |

KT 55

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|----------|-----------------|--------------|
| Depth | 45 mm | Depth (inches) | 1.7716 inch |
| Height | 115 mm | Height (inches) | 4.5275 inch |
| Width | 365 mm | Width (inches) | 14.3701 inch |
| Net weight | 1486.7 g | | |

Environmental Product Compliance

| | |
|------------------------|--------------------------------------|
| RoHS Compliance Status | Not affected |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0 |

Technical data

| | | | |
|------------------------|-----------------------------------------------|---------|---------------------|
| Description of article | Front cable cutter up to 55 mm outer diameter | Version | One-hand mechanical |
|------------------------|-----------------------------------------------|---------|---------------------|

Cutting tools

| | | | |
|------------------------------------------|---------------------|--------------------------------------------------|---------------------|
| Copper sector cable | 3 x 150 SM | Copper cable - flexible, max. (kcmil) | 1000 kcmil |
| Copper cable - flexible, max. | 500 mm ² | Copper cable - stranded, max. (kcmil) | 1000 kcmil |
| Copper cable - stranded, max. | 500 mm ² | Copper cable, max. diameter | 55 mm |
| Data / telephone / control cable, max. Ø | 55 mm | Aluminium sector cable | 4 x 150 SE |
| Stranded aluminium cable, max. (kcmil) | 1000 kcmil | Stranded aluminium cable, max (mm ²) | 500 mm ² |
| Stranded aluminium cable, max. diameter | 55 mm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000142 | ETIM 9.0 | EC000142 |
| ETIM 10.0 | EC000142 | ECLASS 14.0 | 21-04-47-01 |
| ECLASS 15.0 | 21-04-47-01 | | |

Drawings

Example of use

-  Cu + Al: max. 80 mm
-  Cu: max. 630 mm²
Al: max. 1000 mm²
-  Cu: max. 630 mm²



KT 55

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

KT 55



Cutting tools in mechanical ratchet version. Suitable for non-pinch cutting of copper and aluminium conductors. Easy operation thanks to optimum leverage and a cleverly engineered cam mechanism.

General ordering data

| | | |
|------------|----------------------------|--------------------------------|
| Type | ERME KT 55 | Version |
| Order No. | 9204280000 | Replacement parts |
| GTIN (EAN) | 4032248640997 | |
| Qty. | 1 ST | |
| Type | ERTE BAGR 11 KT 55 | Version |
| Order No. | 4316210000 | Cutting tool, Replacement part |
| GTIN (EAN) | 4032248788217 | |
| Qty. | 1 ST | |
| Type | ERTE BAGR 4 KT 55 | Version |
| Order No. | 4316130000 | Cutting tool, Replacement part |
| GTIN (EAN) | 4032248787944 | |
| Qty. | 1 ST | |
| Type | ERTE BAGR 5 KT 55 | Version |
| Order No. | 4316140000 | Cutting tool, Replacement part |
| GTIN (EAN) | 4032248787951 | |
| Qty. | 1 ST | |
| Type | ERTE BAGR 6 KT 55 | Version |
| Order No. | 4316150000 | Cutting tool, Replacement part |
| GTIN (EAN) | 4032248787968 | |
| Qty. | 1 ST | |
| Type | ERTE BAGR 7 KT 55 | Version |
| Order No. | 4316160000 | Cutting tool, Replacement part |
| GTIN (EAN) | 4032248787975 | |
| Qty. | 1 ST | |
| Type | ERTE BAGR 9 KT 55 | Version |
| Order No. | 4316180000 | Cutting tool, Replacement part |
| GTIN (EAN) | 4032248787999 | |
| Qty. | 1 ST | |
| Type | ERME KT 55 | Version |
| Order No. | 9204280000 | Replacement parts |
| GTIN (EAN) | 4032248640997 | |
| Qty. | 1 ST | |
| Type | ERTE BAGR 11 KT 55 | Version |
| Order No. | 4316210000 | Cutting tool, Replacement part |
| GTIN (EAN) | 4032248788217 | |
| Qty. | 1 ST | |
| Type | ERTE BAGR 4 KT 55 | Version |
| Order No. | 4316130000 | Cutting tool, Replacement part |
| GTIN (EAN) | 4032248787944 | |
| Qty. | 1 ST | |

KT 55

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|--------------------------------|
| Type | ERTE BAGR 5 KT 55 | Version |
| Order No. | 4316140000 | Cutting tool, Replacement part |
| GTIN (EAN) | 4032248787951 | |
| Qty. | 1 ST | |
| Type | ERTE BAGR 6 KT 55 | Version |
| Order No. | 4316150000 | Cutting tool, Replacement part |
| GTIN (EAN) | 4032248787968 | |
| Qty. | 1 ST | |
| Type | ERTE BAGR 7 KT 55 | Version |
| Order No. | 4316160000 | Cutting tool, Replacement part |
| GTIN (EAN) | 4032248787975 | |
| Qty. | 1 ST | |
| Type | ERTE BAGR 9 KT 55 | Version |
| Order No. | 4316180000 | Cutting tool, Replacement part |
| GTIN (EAN) | 4032248787999 | |
| Qty. | 1 ST | |