


MULTI-STRIPAX AWG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- For flexible and solid conductors with special insulating materials
- High-quality stripping for industrial applications (complies with aircraft industry requirements)
- Specially shaped blades enable stripping of special types of insulation and conductor configurations
- Stripping length adjustable via end stop
- Very versatile thanks to interchangeable stripping units
- Stripping results reproduced accurately over and over again
- No damage to the conductor
- A long-lasting, reliable tool thanks to its sturdy design
- Integrated cutting function

General ordering data

Version	Tools, Stripping and cutting tool
Order No.	9202230000
Type	MULTI-STRIPAX AWG
GTIN (EAN)	4032248486168
Qty.	1 items

MULTI-STRIPAX AWG

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	40 mm	Depth (inches)	1.5748 inch
Height	85 mm	Height (inches)	3.3464 inch
Width	250 mm	Width (inches)	9.8425 inch
Net weight	520.28 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Technical data

Description of article	Stripping and cutting tool for AWG conductors with PVC and PTFE etc. insulation
------------------------	---

Stripping tools

Cable type	AWG conductor with PTFE and PVC insulation	Copper cable - flexible, max.	6 mm ²
Conductor cross-section (cutting capacity)	6 mm ²	max. cutting capacity, solid	2.5 mm ²
max. cutting capacity, fine-strand	6 mm ²	max. cutting capacity, ribbon	10,2 mm x 4 mm
Stripping range AWG, max.	16 AWG	Stripping range AWG, min.	26 AWG
Stripping length, min.	2 mm	Conductor cross-section, max.	6 mm ²
Conductor cross-section, min.	0.12 mm ²		

Classifications

ETIM 8.0	EC002109	ETIM 9.0	EC002109
ETIM 10.0	EC002109	ECLASS 14.0	21-04-37-06
ECLASS 15.0	21-04-37-06		

MULTI-STRIPAX AWG

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Example of use

