


**WQV 70N/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, Silver grey, 192 A, Number of poles: 3, Pitch in mm (P): 20.50, Insulated: No, Width: 9.5 mm
Order No.	<a href="#">9512250000</a>
Type	WQV 70N/3
GTIN (EAN)	4008190403935
Qty.	5 items

## WQV 70N/3

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	18.6 mm	Depth (inches)	0.7323 inch
Height	51 mm	Height (inches)	2.0079 inch
Width	9.5 mm	Width (inches)	0.374 inch
Net weight	37.75 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	tinned copper	Colour	Silver grey
----------------	---------------	--------	-------------

### System specifications

Version	For the terminals
---------	-------------------

### Additional technical data

Type of fixing	when screwed in	Explosion-tested version	No
----------------	-----------------	--------------------------	----

### Dimensions

Pitch in mm (P)	20.50 mm
-----------------	----------

### General

Number of poles	3
-----------------	---

### Rating data

Rated voltage	400 V	Nominal current	192 A
---------------	-------	-----------------	-------

### Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		

## WQV 70N/3

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Cutting and notching tools for cross-connections



- for Weidmüller Z-Series cross-connections
- for cross-connections from WQV 2.5 to WQV 35
- for cross-connection window of the terminal WSI 6

### General ordering data

Type	WAW 1 NEUTRAL	Version	
Order No.	<a href="#">9004500000</a>	Miscellaneous tools	
GTIN (EAN)	4008190053925		
Qty.	1 ST		

### auxiliary connection



The additional connection enables a separate voltage tap. This can be used, for example, for the emergency power supply before the main switch or simply as an additional connection within the application.

### General ordering data

Type	VH 25.2/8/6.4	Version	
Order No.	<a href="#">1967110000</a>	W-Series, Spacer sleeve	
GTIN (EAN)	4032248739196		
Qty.	5 ST		