

**MP FPC 20/40**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Similar to illustration**



Mounting plates, 1.5 mm sheet steel, galvanised

**General ordering data**

Version	FPC (polycarbonate empty enclosure), Mounting plate, Mounting plate, Height: 160 mm, Width: 360 mm, Depth: 1.5 mm, Basic material: Sheet steel, galvanized, silver
Order No.	<a href="#">9535940000</a>
Type	MP FPC 20/40
GTIN (EAN)	4032248009664
Qty.	1 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	1.5 mm	Depth (inches)	0.0591 inch
Height	160 mm	Height (inches)	6.2992 inch
Width	360 mm	Width (inches)	14.1732 inch
Net weight	656 g		

**Temperatures**

Operating temperature
-----------------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**General information**

Type of fixing	when screwed in	Surface finish	galvanized
Basic material	Sheet steel		

**Classifications**

ETIM 8.0	EC000213	ETIM 9.0	EC000213
ETIM 10.0	EC000213	ECLASS 14.0	27-40-06-39
ECLASS 15.0	27-40-06-39		

**MP FPC 20/40**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Accessories**

**TS 35**

Accessories



**General ordering data**

Type	TS35X7.5 ST FPC 20 VER	Version	
Order No.	<a href="#">8000037558</a>	Rail, TS 35, TS 35 x 7.5, Width: 165 mm, with slot, without slot, Steel,	
GTIN (EAN)	4050118653229	galvanized, chromium-plated	
Qty.	20 ST		

**TS 15**

Accessories



**General ordering data**

Type	TS15X5 ST FPC 20 VER	Version	
Order No.	<a href="#">8000037604</a>	Rail, TS 15, Width: 235 mm, without slot, Steel, galvanized,	
GTIN (EAN)	4050118653168	chromium-plated	
Qty.	20 ST		

**TS 35**

Accessories



**General ordering data**

Type	TS35X7.5 ST FPC 40 HOR	Version	
Order No.	<a href="#">8000037560</a>	Rail, TS 35, TS 35 x 7.5, Width: 365 mm, with slot, without slot, Steel,	
GTIN (EAN)	4050118653243	galvanized, chromium-plated	
Qty.	20 ST		