

## MP FPC 30/40



Mounting plates, 1.5 mm sheet steel, galvanized

### General ordering data

|            |  |
|------------|--|
| Version    | FPC (polycarbonate empty enclosure), Mounting plate, Mounting plate, Height: 260 mm, Width: 360 mm, Depth: 1.5 mm, Basic material: Sheet steel, galvanized, silver |
| Order No.  | <a href="#">9535960000</a>   |
| Type       | MP FPC 30/40   |
| GTIN (EAN) | 4032248009688  |
| Qty.       | 1 items  |

**Technical data**

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Dimensions and weights**

|            |        |                 |              |
|------------|--------|-----------------|--------------|
| Depth      | 1.5 mm | Depth (inches)  | 0.0591 inch  |
| Height     | 260 mm | Height (inches) | 10.2362 inch |
| Width      | 360 mm | Width (inches)  | 14.1732 inch |
| Net weight | 1040 g |                 |              |

**Temperatures**

|                       |
|-----------------------|
| Operating temperature |
|-----------------------|

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**General information**

|                |                 |                |            |
|----------------|-----------------|----------------|------------|
| Type of fixing | when screwed in | Surface finish | galvanized |
| Basic material | Sheet steel     |                |            |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000213    | ETIM 9.0    | EC000213    |
| ETIM 10.0   | EC000213    | ECLASS 14.0 | 27-40-06-39 |
| ECLASS 15.0 | 27-40-06-39 |             |             |

**Accessories**

**TS 35**

Accessories



**General ordering data**

|            |                            |  |  |
|------------|----------------------------|--|--|
| Type       | TS35X7.5 ST FPC 30 VER     | Version  |  |
| Order No.  | <a href="#">8000037561</a> | Rail, TS 35, TS 35 x 7.5, Width: 265 mm, with slot, without slot, Steel, |  |
| GTIN (EAN) | 4050118653250              | galvanized, chromium-plated  |  |
| Qty.       | 20 ST                      |  |  |
| Type       | TS35X7.5 ST FPC 40 HOR     | Version  |  |
| Order No.  | <a href="#">8000037560</a> | Rail, TS 35, TS 35 x 7.5, Width: 365 mm, with slot, without slot, Steel, |  |
| GTIN (EAN) | 4050118653243              | galvanized, chromium-plated  |  |
| Qty.       | 20 ST                      |  |  |