

**STRIPAX 16 ZERT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

**General ordering data**

Version	Tools, Stripping and cutting tool
Order No.	<a href="#">9918180000</a>
Type	STRIPAX 16 ZERT
GTIN (EAN)	4032248371662
Qty.	1 items

## STRIPAX 16 ZERT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	22 mm	Depth (inches)	0.8661 inch
Height	99 mm	Height (inches)	3.8976 inch
Width	190 mm	Width (inches)	7.4803 inch
Net weight	200 g		

## Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

## Technical data

Description of article	Stripping tool for up to 16 mm <sup>2</sup>
------------------------	---

## Stripping tools

Cable type	Flexible and solid conductors with PVC insulation	Conductor cross-section (cutting capacity)	6 mm <sup>2</sup>
Stripping range AWG, max.	6 AWG	Stripping range AWG, min.	10 AWG
Stripping range, min.	6 mm <sup>2</sup>	Stripping length, max.	25 mm
Colour	orange	Conductor cross-section, max.	16 mm <sup>2</sup>
Conductor cross-section, min.	6 mm <sup>2</sup>		

## Important note

Product information	<ul style="list-style-type: none"> <li>• Stripping tools with automatic self-adjustment</li> <li>• For flexible and solid conductors</li> <li>• Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors</li> <li>• Stripping length adjustable via end stop</li> <li>• Automatic opening of clamping jaws after stripping</li> <li>• No fanning-out of individual conductors</li> <li>• Adjustable to diverse insulation thicknesses</li> <li>• Double-insulated cables in two process steps without special adjustment</li> <li>• No play in self-adjusting cutting unit</li> <li>• Long service life</li> <li>• Optimised ergonomic design</li> </ul> Sheathing stripper for PVC cables
---------------------	--

## Classifications

ETIM 8.0	EC002109	ETIM 9.0	EC002109
ETIM 10.0	EC002109	ECLASS 14.0	21-04-37-06
ECLASS 15.0	21-04-37-06		

**STRIPAX 16 ZERT**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

**Example of use**



## STRIPAX 16 ZERT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Accessories / replacement parts



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

## General ordering data

Type	ERME 16 <sup>2</sup> SPX 4	Version
Order No.	<a href="#">1119040000</a>	Accessories, Cutter holder
GTIN (EAN)	4032248948437	
Qty.	1 ST	
Type	ERTE KLBC SPX 16	Version
Order No.	<a href="#">2571490000</a>	Accessories, Replacement clamping jaw
GTIN (EAN)	4050118582116	
Qty.	1 ST	