

## CXX V 71

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergsstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)

## 일반 주문 데이터

버전	CUBESERIES, 보호 바리스터, 정격 제어 전압: 6...24 V AC, 플러그인 결선
주문 번호	<a href="#">3053470000</a>
유형	CXX V 71
GTIN (EAN)	4099987023252
수량	20 items

## 기술 데이터

## 승인

RoHS	준수
------	----

## 치수 및 중량

깊이	23 mm	깊이 (인치)	0.9055 inch
높이	9.2 mm	높이 (인치)	0.3622 inch
너비	12.8 mm	폭 (인치)	0.5039 inch
순중량	2 g		

## 온도

보관 온도	-40 °C...85 °C	주변 온도	-40 °C...70 °C
작동 온도			

## 환경 제품 규정 준수

RoHS 준수 상태	준수, 예외 미존재
REACH SVHC	0.1 wt% 이상의 SVHC 없음

## 제어 측

정격 제어 전압	6...24 V AC	상태 표시기	아니요
보호 회로	바리스터		

## 일반 데이터

UL94 가연성 등급 구성요소	구성요소 UL94 가연성 등급	하우징 V-2
------------------	---------------------	------------

## 결선 데이터

와이어 결선 방식	플러그인 결선
-----------	---------

## 분류

ETIM 8.0	EC002586	ETIM 9.0	EC002586
ETIM 10.0	EC002586	ECLASS 14.0	27-37-16-92
ECLASS 15.0	27-37-16-92		


## CXX V 71

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany


## 도면

[www.weidmueller.com](http://www.weidmueller.com)

## Connection diagram



## Dimensional drawing



## Miscellaneous

## Type code CUBESERIES LED / protective module versions

Product family	□ □ □	□ □	□	□	Input voltage and LED color
C CUBESERIES	□	□	□	□	21N 6-230 V DC
Product type	X	Accessories	□	□	41R 6-24 V DC LED red
X Accessories	□	□	□	□	41G 6-24 V DC LED green
Accessory for which					42R 24-60 V DC LED red
relay design					42G 24-60 V DC LED green
X Universal use					43R 110-230 V DC LED red
Function					43G 110-230 V DC LED green
L LED					51 6-24 V AC/DC
D Free-wheeling diode					52 24-60 V AC/DC
LD LED and free-wheeling diode					53 110-240 V AC/DC
V Varistor					61R 6-24 V AC/DC LED red
RC RC element					61G 6-24 V AC/DC LED green
					62R 24-60 V AC/DC LED red
					62G 24-60 V AC/DC LED green
					63R 110-240 V AC/DC LED red
					63G 110-240 V AC/DC LED green
					71 6-24 V AC
					72 110-130 V AC
					73 220-240 V AC