Data sheet

WK K PZ0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Interchangeable bits for torque screwdriver
Drive output acc. to DIN 5260-PZ, ISO 8764/1-PZ

General ordering data

Version	Screwdriver insert
Order No.	9918600000
Type	WK K PZ0
GTIN (EAN)	4032248388974
Qty.	1 items
Delivery status	Discontinued
Available until	2024-12-04T00:00:00+01:00

Data sheet

WK K PZ0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	4 mm	Depth (inches)	0.1575 inch
Height	4 mm	Height (inches)	0.1575 inch
Width	175 mm	Width (inches)	6.8898 inch
Net weight	25 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1

Technical data

Description of article	Interchangeable bit for crosshead screws, Pozidrive, size 0

Screwing tools

Form	Pozidrive	Size	0
Blade length	175 mm	Torque setting, max.	0.9 Nm

Classifications

ETIM 8.0	EC003864	ETIM 9.0	EC003864
ETIM 10.0	EC003864	ECLASS 14.0	21-04-42-03
ECLASS 15.0	21-04-42-03		

WK K PZ0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Torque screwdriver



If you demand effective and exact work, it is essential to use the precise torque. This also guarantees high repetition accuracy.
This is the perfect job for the new Weidmüller torque screwdriver with the ergonomic grip and the unique interchangeable bit system.

- Compact and especially light design
- Torque set with special tool (supplied); an unintended, incorrect setting is ruled out.
- Ergonomic handle sizes matched to the torque range.
- Tools subjected to routine testing and provided with an ID number; 100% quality control with verification and product reference.
- Clicking sound upon reaching the set torque, clearly audible and noticeable, no unnecessary tightening.
- Interchangeable blades made from high-quality wear-resistant tool steel.
- All tools fulfil the accuracy requirements of: EN ISO 6798, BS EN 26789, ASME B107.14M
- Trigger accuracy +/- 6% of the set scale value.

General ordering data

Type	DMS MANUELL 0,5-1,7	Version
Order No.	9918370000	Torque screwdriver
GTIN (EAN)	4032248388332	
Qty.	1 ST	

Type	DMS MANUELL 2,0-7,0	Version
Order No.	9918380000	Torque screwdriver
GTIN (EAN)	4032248388349	
Qty.	1 ST	