

CXX LD 41R**Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26
D-32758 Detmold
Germanywww.weidmueller.com

Come da figura

Dati generali per l'ordinazione

Versione	CUBESERIES, Modulo LED con diodo a corsa libera, Tensione nominale: 6...24 V DC, Collegamento ad innesto
N. d'ordine	3053290000
Tipo	CXX LD 41R
GTIN (EAN)	4099987023108
CPZ	20 Pieza

CXX LD 41R

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**Omologazioni**

ROHS	Conforme
------	----------

Dimensioni e pesi

Profondità	25.7 mm	Profondità (pollici)	1.0118 inch
Posizione verticale	9.2 mm	Altezza (pollici)	0.3622 inch
Larghezza	12.8 mm	Larghezza (pollici)	0.5039 inch
Peso netto	2 g		

Temperature

Temperatura di magazzinaggio	-40 °C...85 °C	Temperatura ambiente	-40 °C...70 °C
Temperatura d'esercizio			

Conformità ambientale del prodotto

Stato conformità RoHS	Conforme senza esenzione
REACH SVHC	No SVHC superiori a 0,1 wt%

Iato di comando

Tensione nominale	6...24 V DC	Corrente nominale DC	6.8 mA
Indicatore di stato	LED rosso	Circuito di protezione	Diodo a corsa libera

Dati generali

Colori	nero
Componente classe d'infiammabilità UL94	Componente Classe d'infiammabilità UL94

Dati di collegamento

Tecnica di collegamento cavi	Collegamento ad innesto
------------------------------	-------------------------



Classificazioni

ETIM 8.0	EC002586	ETIM 9.0	EC002586
ETIM 10.0	EC002586	ECLASS 14.0	27-37-16-92
ECLASS 15.0	27-37-16-92		

CXX LD 41R

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings**Connection diagram****Dimensional drawing**

CXX LD 41R

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Drawings**Miscellaneous****Type code CUBESERIES LED / protective module versions**

Product family	<input type="checkbox"/>	Input voltage and LED color					
C CUBESERIES							21N 6-230 V DC
Product type	<input type="checkbox"/>						41R 6-24 V DC LED red
X Accessories							41G 6-24 V DC LED green
Accessory for which relay design	<input type="checkbox"/>						42R 24-60 V DC LED red
X Universal use							42G 24-60 V DC LED green
Function	<input type="checkbox"/>						43R 110-230 V DC LED red
L LED							43G 110-230 V DC LED green
D Free-wheeling diode							51 6-24 V AC/DC
LD LED and free-wheeling diode							52 24-60 V AC/DC
V Varistor							53 110-240 V AC/DC
RC RC element							61R 6-24 V AC/DC LED red
							61G 6-24 V AC/DC LED green
							62R 24-60 V AC/DC LED red
							62G 24-60 V AC/DC LED green
							63R 110-240 V AC/DC LED red
							63G 110-240 V AC/DC LED green
							71 6-24 V AC
							72 110-130 V AC
							73 220-240 V AC