


## CXX RC 51

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergsstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



## 일반 주문 데이터

버전	CUBESERIES, RC 요소, 정격 제어 전압: 6~24 V UC, 플러그인 결선
주문 번호	<a href="#">3053370000</a>
유형	CXX RC 51
GTIN (EAN)	4099987023160
수량	20 items

## CXX RC 51

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## 기술 데이터

## 승인

ROHS	준수
------	----

## 치수 및 중량

깊이	23 mm	깊이 (인치)	0.9055 inch
높이	9.2 mm	높이 (인치)	0.3622 inch
너비	12.8 mm	폭 (인치)	0.5039 inch
순중량	2 g		

## 온도

보관 온도	-40 °C...85 °C	주변 온도	-40 °C...70 °C
작동 온도			

## 환경 제품 규정 준수

RoHS 준수 상태	준수, 예외 미존재
REACH SVHC	0.1 wt% 이상의 SVHC 없음

## 제어 측

정격 제어 전압	6...24 V UC	정격 전류 AC	1.5 mA
상태 표시기	아니요	보호 회로	RC 요소

## 일반 데이터

컬러 코드	검정				
UL94 가연성 등급 구성요소	<table> <tr> <td>구성요소</td> <td>하우징</td> </tr> <tr> <td>UL94 가연성 등급</td> <td>V-2</td> </tr> </table>	구성요소	하우징	UL94 가연성 등급	V-2
구성요소	하우징				
UL94 가연성 등급	V-2				

## 결선 데이터

와이어 결선 방식	플러그인 결선
-----------	---------

## 분류

ETIM 6.0	EC002586	ETIM 7.0	EC002586
ETIM 8.0	EC002586	ETIM 9.0	EC002586
ETIM 10.0	EC002586	ECLASS 9.1	27-37-10-10
ECLASS 10.0	27-37-10-10	ECLASS 11.0	27-37-16-92
ECLASS 12.0	27-37-16-92	ECLASS 13.0	27-37-16-92
ECLASS 14.0	27-37-16-92	ECLASS 15.0	27-37-16-92


## CXX RC 51

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany


## 도면

[www.weidmueller.com](http://www.weidmueller.com)

## Connection diagram



## Dimensional drawing



## Miscellaneous

## Type code CUBESERIES LED / protective module versions

Product family	□ □ □	□ □	□	□	Input voltage and LED color
C CUBESERIES	□	□	□	□	21N 6-230 V DC
Product type	X	Accessories	□	□	41R 6-24 V DC LED red
X Accessories	□	□	□	□	41G 6-24 V DC LED green
Accessory for which	□	□	□	□	42R 24-60 V DC LED red
relay design	□	□	□	□	42G 24-60 V DC LED green
X Universal use	□	□	□	□	43R 110-230 V DC LED red
Function	□	□	□	□	43G 110-230 V DC LED green
L LED	□	□	□	□	51 6-24 V AC/DC
D Free-wheeling diode	□	□	□	□	52 24-60 V AC/DC
LD LED and free-wheeling diode	□	□	□	□	53 110-240 V AC/DC
V Varistor	□	□	□	□	61R 6-24 V AC/DC LED red
RC RC element	□	□	□	□	61G 6-24 V AC/DC LED green
			□	□	62R 24-60 V AC/DC LED red
			□	□	62G 24-60 V AC/DC LED green
			□	□	63R 110-240 V AC/DC LED red
			□	□	63G 110-240 V AC/DC LED green
			□	□	71 6-24 V AC
			□	□	72 110-130 V AC
			□	□	73 220-240 V AC