



通用订货数据

|            |                                                                                                 |
|------------|-------------------------------------------------------------------------------------------------|
| 版本         | 系统电缆, M12 D 编码 – IP 67 直型插座, 打开的, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), Radox GKW S, 3 m |
| 订货号        | <a href="#">1309790030</a>                                                                      |
| 类型         | IE-C5DB4RE0030MSSXXX-E                                                                          |
| GTIN (EAN) | 4050118120820                                                                                   |
| 数量         | 1 items                                                                                         |

## IE-C5DB4RE0030MSSXXX-E

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## 技术数据

## 审批

ROHS 一致

## 尺寸和重量

|    |       |         |               |
|----|-------|---------|---------------|
| 长度 | 3 m   | 长度 (英寸) | 118.1102 inch |
| 净重 | 144 g |         |               |

## 温度

|      |                |      |                |
|------|----------------|------|----------------|
| 存储温度 | -40 °C...90 °C | 工作温度 | -40 °C...90 °C |
| 安装温度 | -25 °C...90 °C |      |                |

## 环保产品合规

|                  |                                      |
|------------------|--------------------------------------|
| RoHS 合规状态        | 合规, 有例外                              |
| RoHS 豁免 (如适用/已知) | 6c                                   |
| REACH SVHC       | Lead 7439-92-1                       |
| SCIP             | 67cf1078-beca-4687-860b-dc475a6ec24a |

## 电缆专用标准

|             |                                                                                                                                      |              |                                                                          |
|-------------|--------------------------------------------------------------------------------------------------------------------------------------|--------------|--------------------------------------------------------------------------|
| 总线阻燃性       | 符合 ISO 6722-1 5.22 (UN ECE-R 118.01) 标准                                                                                              | 氟含量          | According to EN 60684-2 Section 45.2                                     |
| 电缆束上的垂直火花扩散 | According to BS4066-3, DIN EN 50266-2-5, According to IEC 60332-3-25 D                                                               | 多芯线金属数据和控制电缆 | According to EN50288-2-2                                                 |
| 卤化氢含量       | According to EN-50267-2-1, According to IEC 60754-1                                                                                  | 燃气的腐蚀性       | to IEC 60754-2                                                           |
| 轨道车防火       | According to DIN 5510-2 fire safety levels 1,2,3,4, According to BS 6853, According to EN50288-2-2, According to EN 45545, HL1 - HL3 | 烟雾密度         | According to BS 6853 Appendix D, 符合 EN 50268-2, According to IEC 61034-2 |
| 有毒气体        | According to BS 6853 Appendix B                                                                                                      |              |                                                                          |

## 右插头

插头, 右 自由导线端

## 左插头

插头, 左 M12, D-编码, IP67, 孔式端头, 笔直, 插头, 塑料, 带屏蔽

## 插头

|       |       |       |                                        |
|-------|-------|-------|----------------------------------------|
| 插头, 右 | 自由导线端 | 插头, 左 | M12, D-编码, IP67, 孔式端头, 笔直, 插头, 塑料, 带屏蔽 |
|-------|-------|-------|----------------------------------------|

## 电缆电气属性

|     |                                             |
|-----|---------------------------------------------|
| 目录册 | Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B) |
|-----|---------------------------------------------|

## 技术数据

## 电缆的机械和材料属性

|            |                                                                          |        |                     |
|------------|--------------------------------------------------------------------------|--------|---------------------|
| 防油         | in accordance with EN 50306-3                                            | 卤素     | 无卤, 符合IEC 60754-2标准 |
| 最小弯曲半径, 多次 | 6 *直径                                                                    | 抗磨性    | 非常好                 |
| 阻燃性        | in accordance with IEC 60332-1-2                                         | 燃气的腐蚀性 | to IEC 60754-2      |
| 烟雾密度       | According to BS 6853 Appendix D, 符合 EN 50268-2, According to IEC 61034-2 |        |                     |

## 电缆结构

|        |                                         |        |             |
|--------|-----------------------------------------|--------|-------------|
| 绞合线    | 7                                       | 护套颜色   | 黑色, SF/UTP  |
| 截面积    | 2*2*AWG 22/7 - 2*2*0.36 mm <sup>2</sup> | 屏蔽     | SF/UTP      |
| 绝缘横截面  | 1.95 mm                                 | 最大护套直径 | 7.55 mm     |
| 最小护套直径 | 6.95 mm                                 | 护套材料   | Radox GKW S |

## 分类

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002599    | ETIM 9.0    | EC002599    |
| ETIM 10.0   | EC002599    | ECLASS 14.0 | 27-06-03-08 |
| ECLASS 15.0 | 27-06-03-08 |             |             |