


CMA-RCM-DACT-120

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

与插图相似



Difference current transformer (Residual current monitoring, RCM)

This type is specialised in the detection of residual currents in 3 / 4-wire AC networks.

Its special features are:

Highly sensitive current sensor for the detection of even the smallest residual currents, fixed switching hysteresis of 5%, high safety thanks to integrated overvoltage protection and coverage of a wide frequency range.

通用订货数据

版本	剩余电流互感器, 初级电流: 25 A, 圆导线: 120.00 mm, 已关闭电流互感器
订货号	2603450000
类型	CMA-RCM-DACT-120
GTIN (EAN)	4050118665406
数量	1 items
本地产品	仅在特定国家有售
厂商	MBS AG

CMA-RCM-DACT-120

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

技术数据

审批

ROHS 一致

通用订货数据

本地产品 仅在特定国家有售

尺寸和重量

深	37 mm	深度 (英寸)	1.4567 inch
高度	191.5 mm	高度 (英寸)	7.5394 inch
宽度	210 mm	宽度 (英寸)	8.2677 inch
净重	240 g		

温度

存储温度 -25 °C...70 °C 工作温度 -10 °C...70 °C

环保产品合规

RoHS 合规状态 符合要求
REACH SVHC 不超过 0.1 wt% 的高度关注物质 (SVHC)

带电导线的尺寸

导线类型	仅绝缘导体	圆导线	120.00 mm
安装位置	室内使用		

技术特性

防护等级	I	测量精度	1 类 (IEC 6206-21)
线圈电阻	8 Ω		

电气特性

精度等级	1	次级电流	0...0.04 A
传输速率	1:600	负载	0 VA
频带	30 Hz...3 kHz	初级电流	25 A

测量电流输入

剩余电流测量 是

输入

输入测量范围 0.02...2 A / 0.25...25 A 取决于端子分配

绝缘参数

标准	EN 60044/1	抗冲击耐压	8 kV
污染等级	3	绝缘	是
精度等级	1	额定电压	800 V

分类

ETIM 8.0	EC002048	ETIM 9.0	EC002048
ETIM 10.0	EC002048	ECLASS 14.0	27-21-09-02
ECLASS 15.0	27-21-09-02		

