

QB 25/6.5/11.5 SAKR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Cross-connector (terminal), when screwed in, grey, 32 A, Number of poles: 25, Pitch in mm (P): 6.50, Insulated: No, Width: 0.9 mm
Order No.	0134000000
Type	QB 25/6.5/11.5 SAKR
GTIN (EAN)	4008 1901 18945
Qty.	20 items

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	13.24 mm	Depth (inches)	0.5213 inch
Height	158.6 mm	Height (inches)	6.2441 inch
Width	0.9 mm	Width (inches)	0.0354 inch
Net weight	7.84 g		

Temperatures

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
REACH SVHC No SVHC above 0.1 wt%

Material data

Basic material Cu Zn Colour grey

System specifications

Version for cross-connection link

Additional technical data

Type of fixing when screwed in Installation advice Direct mounting
Type of mounting when screwed in

Dimensions

Pitch in mm (P) 6.50 mm

General

Number of poles 25 Installation advice Direct mounting

Rating data

Nominal current 32 A

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		