

Weidmüller Interface GmbH & Co. KG

1

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Product image**







Similar to illustration

In some applications it is useful to protect the feed through connection with a separate fuse. Fuse terminal blocks are made up of one terminal block bottom section with a fuse insertion carrier. The fuses vary from pivoting fuse levers and pluggable fuse holders to screwable closures and flat plug-in fuses.

## **General ordering data**

Version	Fuse terminal, Screw connection, medium yellow, 10 mm², 16 A, 400 V, Number of connections: 2, Number of levels: 1, TS 32
Order No.	<u>0162220000</u>
Туре	SAKS 4 USA
GTIN (EAN)	4008190016586
Qty.	20 items
Delivery status	This article will no longer be available in the future.
Available until	2026-06-30T00:00:00+02:00
Alternative product	WSI 25/1 10X38





## Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Technical data**

Approvals			
Approvals			
трргочиз	<b>(€</b> ®•	<b>SY</b> EK	
ROHS	Conform		
UL File Number Search	UL Website		
Certificate No. (UR)	E60693		
Dimensions and weights			
Depth	73 mm	Depth (inches)	2.874 inch
Height	75 mm	Height (inches)	2.9527 inch
Width	24 mm	Width (inches)	0.9449 inch
Net weight	92.7 g		
Temperatures			
Storage temperature	-25 °C55 °C	Ambient temperature	-5 °C40 °C
Continuous operating temp., min.	-20 °C	Ambient temperature Continuous operating temp., max.	-5 C40 C
continuous operating temp., min.	-00 C	Continuous operating temp., max.	130 C
RoHS Compliance Status REACH SVHC  Material data	Compliant without exemption No SVHC above 0.1 wt%		
Basic material	KrG	Colour	medium yellov
UL 94 flammability rating	V-0, 5VA		
System specifications			
Version	Screw connection, Fuse cartridge, One end without connector	End cover plate required	No
Number of potentials	1	Number of levels	1
Number of clamping points per level	2	Levels cross-connected internally	No
PE connection	No	Mounting rail	TS 32
N-function	No	PE function	No
PEN function	No		
Additional technical data			
Onen sides	closed	Number of similar terminals	1
	closed  Direct mounting	Number of similar terminals  Explosion-tested version	1 No
Open sides Installation advice Type of mounting	closed Direct mounting Snap-on	Number of similar terminals  Explosion-tested version	1 No
Installation advice Type of mounting	Direct mounting		
Installation advice Type of mounting  CSA rating data	Direct mounting Snap-on	Explosion-tested version	No
Type of mounting  CSA rating data  Wire cross section max. (CSA)	Direct mounting Snap-on  8 AWG	Explosion-tested version  Voltage size C (CSA)	No 600 V
Installation advice Type of mounting	Direct mounting Snap-on	Explosion-tested version	No

Creation date 05.11.2025 03:21:33 MEZ

Voltage size D (CSA)

Wire cross section min. (CSA)

Catalogue status / Drawings

Current size D (CSA)

5 A

2

600 V

22 AWG



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

Conductors for clamping (additional connection)
---

Connection type, additional connection Screw connection

## **Conductors for clamping (rated connection)**

Gauge to IEC 60947-1	B6	Wire connection cross section AWG, max.	AWG 8
Connection direction	on side	Tightening torque, max.	2.4 Nm
Tightening torque, min.	1.2 Nm	Stripping length	14 mm
Type of connection 2	Screw connection	Type of connection	Screw connection
Number of connections	2	Clamping range, max.	16 mm²
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping screw	M 4
Blade size	1.0 x 5.5 mm	Wire connection cross section AWG, min.	AWG 20
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	10 mm²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.5 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	10 mm²
Wire connection cross section, finely stranded, min.	0.5 mm²	Connection cross-section, stranded, max.	10 mm²
Connection cross-section, stranded, mi	n. 0.5 mm²	Torque level with DMS electric screwdriver	4
Wire connection cross-section, solid core, max.	16 mm²	Wire connection cross-section, solid core, min.	0.5 mm²
Connection cross-section, finely stranded, min.	0.5 mm <sup>2</sup>		

## General

Wire connection cross section AWG,	AWG 8	Installation advice	Direct mounting
max.			
Wire connection cross section AWG,	AWG 20	Standards	IEC 60947-7-3
min.			
Mounting rail	TS 32		

## **Rating data**

Rated cross-section	10 mm <sup>2</sup>	Rated voltage	400 V
Rated DC voltage	400 V	Nominal current	16 A
Current at maximum wires	30 A	Standards	IEC 60947-7-3
Volume resistance according to IEC 60947-7-x	0.56 mΩ	Rated impulse withstand voltage	6 kV
Power loss in accordance with IEC 60947-7-x	1.82 W	Pollution severity	3

## **UL** rating data

Conductor size Factory wiring max. (UR) 8 AWG		Current size C (UR)	30 A
Voltage size C (UR)	600 V	Conductor size Factory wiring min. (UR)	26 AWG
Certificate No. (UR)	E60693	Conductor size Field wiring min. (UR)	22 AWG
Conductor size Field wiring max. (UR)	8 AWG		

## Important note

Product information	The voltage depends on the selected fuse element or the selected indicator light

Creation date 05.11.2025 03:21:33 MEZ





## Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

## Classifications

ETIM 6.0	EC000899	ETIM 7.0	EC000899
ETIM 8.0	EC000899	ETIM 9.0	EC000899
ETIM 10.0	EC000899	ECLASS 9.0	27-14-11-16
ECLASS 9.1	27-14-11-16	ECLASS 10.0	27-14-11-16
ECLASS 11.0	27-14-11-16	ECLASS 12.0	27-14-11-16
ECLASS 13.0	27-25-01-13	ECLASS 14.0	27-25-01-13
ECLASS 15.0	27-25-01-13		



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Accessories

#### **Cross-connections**









The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## **General ordering data**

Туре	QL 2 SAKS4	Version
Order No.	0328000000	Cross-connector (terminal), when screwed in, grey, 47 A, Number of
GTIN (EAN)	4008190071165	poles: 2, Pitch in mm (P): 24.00, Insulated: No, Width: 34 mm
Qty.	20 ST	
Туре	QL 3 SAKS4	Version
Type Order No.	QL 3 SAKS4 0328100000	Version Cross-connector (terminal), when screwed in, grey, 47 A, Number of
• •		

## **Disconnect plugs**



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

## **General ordering data**

Туре	QL 10 SAKS4	Version
Order No.	0339000000	Cross-connector (terminal), when screwed in, grey, 47 A, Number of
GTIN (EAN)	4008190025335	poles: 10, Pitch in mm (P): 10.00, Insulated: No, Width: 226 mm
Qty.	20 ST	

### **Mounting support**



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.



## Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# Accessories

## **General ordering data**

Type	SS M4 D 128-A 4	Version
Order No.	0136400000	Lock washer, Copper
GTIN (EAN)	4008190118143	
Qty.	100 ST	
Type	BFSC M4X9T	Version
Type Order No.	BFSC M4X9T 0103300000	Version Mounting screw (Terminal), 4.00 mm, Steel, Depth: 7 mm, Width: 7

### Fuse









As accessories for our wide product portfolio of fuse terminal blocks, we also offer the appropriate fuse links. The portfolio includes device protection fuses (miniature fuses) from 5x20 mm up to 10x38 mm, E 14 to E 18 fuse links, as well as automotive fuses and automatic circuit breakers. Gauge rings for the fuse holders round off the overall portfolio.

## **General ordering data**

<b>C</b> 0	oraoring aata	
Туре	E 14/2A RS	Version
Order No.	0137400000	Active components, Cartridge fuse
GTIN (EAN)	4008190069094	
Qty.	10 ST	
Туре	E 14/4A BR	Version
Order No.	<u>0137500000</u>	Active components, Cartridge fuse
GTIN (EAN)	4008190142629	
Qty.	10 ST	
Туре	E 14/6A GN	Version
Order No.	0328300000	Active components, Cartridge fuse
GTIN (EAN)	4008190002190	
Qty.	10 ST	
Туре	E 14/10A RT	Version
Order No.	0328400000	Active components, Cartridge fuse
GTIN (EAN)	4008190000288	
Qty.	10 ST	
Туре	E 14/16A GR	Version
Order No.	0328500000	Active components, Cartridge fuse
GTIN (EAN)	4008190152161	
Qty.	10 ST	
Туре	P 14/2 D01 RS SAKS4	Version
Order No.	<u>0138000000</u>	Fuse gauge ring (terminal), Height: 11 mm, Depth: 10.5 mm,
GTIN (EAN)	4008190114664	Aluminium, pink
Qty.	50 ST	
Туре	P 14/6 D01 GN SAKS4	Version
Order No.	0328600000	Fuse gauge ring (terminal), Height: 11 mm, Depth: 10.5 mm,
GTIN (EAN)	4008190004248	Aluminium, green
Qty.	50 ST	

Creation date 05.11.2025 03:21:33 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

Type	P 14/10 D01 RT SAKS4	Version
Order No.	0328700000	Fuse gauge ring (terminal), Height: 11 mm, Depth: 10.5 mm,
GTIN (EAN)	4008190010294	Aluminium, red
Qty.	50 ST	
Туре	P 14/4 D01 BR SAKS4	Version
Type Order No.	P 14/4 D01 BR SAKS4 0138100000	Version Fuse gauge ring (terminal), Height: 11 mm, Depth: 10.5 mm,
	,	

### **Fuse holder**



The fuse holder SIHA quickly turns a disconnect terminal into a fuse terminal: simply remove the disconnect lever and attach the fuse unit.

### **General ordering data**

Туре	SK E14 SAKS4	Version
Order No.	<u>0339410000</u>	Screw cover cap (terminal)
GTIN (EAN	N) 4008190032104	
Qty.	20 ST	

## **Custom printing**



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### **General ordering data**

Type	DEK 5/5 MC SDR	Version
Order No.	<u>1609810000</u>	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4008190456597	Weidmueller, To customer specification
Qty.	200 ST	

Creation date 05.11.2025 03:21:33 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Accessories

#### Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### **General ordering data**

Type DEK 5/5 MC NE WS
Order No. 1609801044
GTIN (EAN) 4008190397111
Oty. 1000 ST

Version

Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00

Weidmueller, white

#### SchT group marker carrier



The SchT 5 S group tag carriers are clipped directly onto the TS 32 mounting rail (G-rail) or the TS 35 mounting rail (top-hat rail). It is therefore possible to label the terminal strip irrespective of the terminal and the type of terminal. SchT 5 and SchT 5 S are fitted with ESO 5, STR 5 protective strips.

The SchT 7 is a hinged group tag carrier for inlay tags which enables easy access to the clamping screw.

The SchT 7 is fitted with ESO 7, STR 7 protective strips or DEK 5.

Inlay tags and protective strips can be found under "Accessories".

## **General ordering data**

Type SCHT 7
Order No. 0517960000
GTIN (EAN) 4008190001742
Oty. 20 ST

Version

SCHT, Terminal marker, 39.3 x 8 mm, Pitch in mm (P): 7.00

Weidmueller, white

Creation date 05.11.2025 03:21:33 MEZ



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Accessories

#### **End bracket**









Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

### General ordering data

Type	EW 35	Version
Order No.	0383560000	End bracket, beige, TS 35, V-2, Wemid, Width: 8.5 mm, 100 °C
GTIN (EAN)	4008190181314	
Qty.	50 ST	
Туре	EWK 1	Version
	EWK 1 0206160000	Version End bracket, beige, TS 32, V-0, Wemid, Width: 9 mm, 100 °C
Order No.		

## **Custom printing**



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## **General ordering data**

7	Гуре	DEK 5/6.5 MC SDR	Version
(	Order No.	<u>1609850000</u>	Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50
(	GTIN (EAN)	4008190456610	Weidmueller, To customer specification
C	Ωty.	180 ST	

Creation date 05.11.2025 03:21:33 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

#### Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### **General ordering data**

Qty.

Туре	DEK 5/6.5 MC NE WS
Order No.	1609840000
GTIN (EAN)	4008190203429

900 ST

Version

Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50

Weidmueller, white

#### **End plates and partition plates**



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

## **General ordering data**

Туре	WTW EN	Version
Order No.	1058800000	Partition plate (terminal), dark beige, Height: 86 mm, Width: 3 mm,
GTIN (EAN)	4008190140175	V-0, Wemid
Qty.	20 ST	

#### **End bracket**









Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

Creation date 05.11.2025 03:21:33 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

General	ordering	data
General	oraeming	uata

Type	EWK 1 ALT	Version
Order No.	0495160000	End bracket, beige, TS 32, V-2, Polyamide 66, Width: 8 mm, 100 °C
GTIN (EAN)	4008190160777	
Qty.	50 ST	
Туре	EWK 2	Version
Order No.	0199360000	End bracket, beige, TS 32, V-0, Wemid, Width: 15 mm, 100 °C
GTIN (EAN)	4008190023546	
Qty.	50 ST	
Туре	WEW 32/1	Version
Order No.	1067600000	End bracket, dark beige, TS 32, V-2, PA 66 GF 30, Width: 12 mm,
GTIN (EAN)	4008190099657	100 °C
Qty.	50 ST	

## **Custom printing**



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- · Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## **General ordering data**

Туре	DEK 5/6 MC SDR	Version
Order No.	1609830000	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4008190456603	Weidmueller, To customer specification
Qty.	200 ST	

Creation date 05.11.2025 03:21:33 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Accessories

#### **Blank**



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

#### **General ordering data**

Туре	DEK 5/6 MC NE WS	Version
Order No.	<u>1609820000</u>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4008190203436	Weidmueller, white
Qty.	1000 ST	
Туре	DEK 5/8 MC NE WS	Version
Type Order No.	DEK 5/8 MC NE WS 1856740000	Version  Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
	· ·	

### **Custom printing**



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## **General ordering data**

Creation date 05.11.2025 03:21:33 MEZ

Type	DEK 5/8 MC SDR	Version
Order No.	<u>1856750000</u>	Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
GTIN (EAN)	4032248400867	Weidmueller, To customer specification
Qty.	160 ST	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Accessories

#### Plus



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- · Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## **General ordering data**

Type DEK 5/8 PLUS MC NE WS
Order No. 1046350000
GTIN (EAN) 4032248782055

N) 4032248782055 800 ST Version

Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00

Weidmueller, white

#### **Custom printing**

Qty.



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### **General ordering data**

Type DEK 5/8 PLUS MC SDR
Order No. 1046370000
GTIN (EAN) 4032248782079
Oty. 160 ST

Version

Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00

Weidmueller, To customer specification

Creation date 05.11.2025 03:21:33 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Accessories

### **DEK 5/8**



#### WS/DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- · Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- · Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

### **General ordering data**

Туре	DEK 5/8 MM WS	Version
Order No.	2007130000	Dekafix, Terminal marker, 5 x 8 mm, Weidmueller, white
GTIN (EAN)	4050118392012	
Qty.	500 ST	

## Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snaped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

## **General ordering data**

Type	BZT 1 WS 10/5	Version
Order No.	1805490000	Accessories, Marker holder
GTIN (EAN)	4032248270231	
Qty.	100 ST	
Туре	BZT 1 ZA WS 10/5	Version
Order No.	1805520000	Accessories, Marker holder
	100002000	Accessories, Market Holder
GTIN (EAN)	4032248270248	Accessories, Market Holder

Creation date 05.11.2025 03:21:33 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

### **DEK 5/6**



#### WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- · Firm hold and durable printing
- · Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

## **General ordering data**

Туре	DEK 5/6 MM WS	Version
Order No.	2007120000	Dekafix, Terminal marker, 5 x 6 mm, Weidmueller, white
GTIN (EAN)	4050118392104	
Qty.	600 ST	