

EGT1 EG2/EN SCHALT.1X1U**Weidmüller Interface GmbH & Co. KG**


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product is no longer available,
Data sheet for information only



The profiles of the switch and button components match those of the electronic components.

Switches and buttons facilitate commissioning, servicing, monitoring and repair of industrial installations.

General ordering data

Version	, Function component Circuit breaker, Screw connection
Order No.	0126360000
Type	EGT1 EG2/EN SCHALT.1X1U
GTIN (EAN)	4008190097141
Qty.	10 items
Delivery status	Discontinued
Available until	2024-10-22T00:00:00+02:00

EGT1 EG2/EN SCHALT.1X1U

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Height	50 mm	Height (inches)	1.9685 inch
Width	18 mm	Width (inches)	0.7087 inch
Length	58 mm	Length (inches)	2.2835 inch
Net weight	35.99 g		

Temperatures

Storage temperature -40 °C... 100 °C Operating temperature -25 °C... 85 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Mounting rail TS 32, TS 35

Output

Rated switching voltage	250 V AC	AC switching capacity (resistive), max.	1500 VA @ 250 V
AC switching capacity, max.	1500 VA	Switching capacity	250 V
DC switching capacity (resistive), max.	180 W @ 30 V	DC switching capacity, max.	180 W
Switching capacity	30 V		

General data

Mounting rail TS 32, TS 35 Colour beige

Connection data

Wire connection method	Screw connection	Clamping range, rated connection	6 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	6 mm ²
Wire connection cross section, finely stranded, max.	4 mm ²		

Classifications

ETIM 6.0	EC002498	ETIM 7.0	EC002498
ETIM 8.0	EC002498	ETIM 9.0	EC002498
ETIM 10.0	EC002498	ECLASS 9.0	27-37-92-01
ECLASS 9.1	27-37-92-01	ECLASS 10.0	27-37-13-92
ECLASS 11.0	27-37-13-92	ECLASS 12.0	27-37-13-92
ECLASS 13.0	27-37-13-92	ECLASS 14.0	27-37-13-92
ECLASS 15.0	27-37-13-92		

EGT1 EG2/EN SCHALT.1X1U

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Steel




Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Type	TS 32X15 2M/ST/ZN	Version
Order No.	0122800000	Terminal rail, Accessories, Steel, galvanic zinc plated and passivated,
GTIN (EAN)	4008190066307	Width: 2000 mm, Height: 33 mm, Depth: 15 mm
Qty.	20 M	

End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Type	EWK 2	Version
Order No.	0199360000	End bracket, beige, TS 32, V-0, Wemid, Width: 15 mm, 100 °C
GTIN (EAN)	4008190023546	
Qty.	50 ST	

Steel



Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.


General ordering data

Type	TS 35X7.5 2M/ST/ZN	Version
Order No.	0383400000	Terminal rail, Accessories, Steel, galvanic zinc plated and passivated,
GTIN (EAN)	4008190088026	Width: 2000 mm, Height: 35 mm, Depth: 7.5 mm
Qty.	40 M	

EGT1 EG2/EN SCHALT.1X1U

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories
End bracket


Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Type	EW 35	Version
Order No.	0383560000	End bracket, beige, TS 35, V-2, Wemid, Width: 8.5 mm, 100 °C
GTIN (EAN)	4008190181314	
Qty.	50 ST	

Steel


Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Type	TS 35X15/2.3 2M/ST/ZN	Version
Order No.	0498000000	Terminal rail, Accessories, Steel, galvanic zinc plated and passivated,
GTIN (EAN)	4008190042493	Width: 2000 mm, Height: 35 mm, Depth: 15 mm
Qty.	20 M	