

**VL 2 SAK16/SAKA****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

|                 |                                                                                                                                 |
|-----------------|---------------------------------------------------------------------------------------------------------------------------------|
| Version         | Cross-connector (terminal), when screwed in, grey, 57 A, Number of poles: 2, Pitch in mm (P): 12.00, Insulated: No, Width: 8 mm |
| Order No.       | <a href="#">0135800000</a>                                                                                                      |
| Type            | VL 2 SAK16/SAKA                                                                                                                 |
| GTIN (EAN)      | 4008190132088                                                                                                                   |
| Qty.            | 50 items                                                                                                                        |
| Delivery status | This article will no longer be available in the future.                                                                         |
| Last order date | 2026-06-30T00:00:00+02:00                                                                                                       |

## VL 2 SAK16/SAKA

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 1.5 mm | Depth (inches)  | 0.0591 inch |
| Height     | 20 mm  | Height (inches) | 0.7874 inch |
| Width      | 8 mm   | Width (inches)  | 0.315 inch  |
| Net weight | 1.23 g |                 |             |

## Temperatures

|                     |                |                     |               |
|---------------------|----------------|---------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
|---------------------|----------------|---------------------|---------------|

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Material data

|                |       |        |      |
|----------------|-------|--------|------|
| Basic material | Cu Zn | Colour | grey |
|----------------|-------|--------|------|

## System specifications

|         |                 |
|---------|-----------------|
| Version | Cross-connector |
|---------|-----------------|

## Additional technical data

|                          |                 |                     |                 |
|--------------------------|-----------------|---------------------|-----------------|
| Type of fixing           | when screwed in | Installation advice | Direct mounting |
| Explosion-tested version | No              | Type of mounting    | when screwed in |

## Dimensions

|                 |          |
|-----------------|----------|
| Pitch in mm (P) | 12.00 mm |
|-----------------|----------|

## General

|                 |   |                     |                 |
|-----------------|---|---------------------|-----------------|
| Number of poles | 2 | Installation advice | Direct mounting |
|-----------------|---|---------------------|-----------------|

## Rating data

|               |       |                 |      |
|---------------|-------|-----------------|------|
| Rated voltage | 400 V | Nominal current | 57 A |
|---------------|-------|-----------------|------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000489    | ETIM 9.0    | EC000489    |
| ETIM 10.0   | EC000489    | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 |             |             |