

TS 32X15 2M/AL/BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

Aluminum has the second best electrical conductivity after copper. One advantage is low weight, another is outstanding corrosion protection.

General ordering data

Version	Terminal rail, Accessories, Aluminium, untreated, Width: 2000 mm, Height: 33 mm, Depth: 15 mm
Order No.	0169300000
Type	TS 32X15 2M/AL/BK
GTIN (EAN)	4008190105167
Qty.	20 M

TS 32X15 2M/AL/BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	15 mm	Depth (inches)	0.5906 inch
Height	33 mm	Height (inches)	1.2992 inch
Width	2000 mm	Width (inches)	78.74 inch
Net weight	235.5 g		

Temperatures

Ambient temperature	-5 °C...40 °C
---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Mounting rail

Installation advice	Direct mounting	
Standards	DIN EN 60715	
Surface finish	untreated	
Thickness	1.50 mm	
Basic material	Aluminium	
Length of the terminal rail	min.	0 mm
	nominal	2000 mm
	max.	2000 mm
Permitted thermal current for PEN function, max.	192.00 A	
Short-time withstand current per second according to IEC 60947-7-2	8.4 kA	
Pre-punched mounting rail	No	
Slit width		
Short circuit strength corresponds to E-Cu wire	70.00 mm ²	
Spacing of holes, centre-to-centre	0 mm	
Slit gap		
Slit length		

Classifications

ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		

